



MATERIAL

stem-polypropylene white
 float-polypropylene white
 Nut-polypropylene white
 O-ring nitril cautchouc black
 lock-washer-polypropylene white
 Schaft-Polypropylen weiss
 Schwimmer-Polypropylen weiss
 Mutter-Polypropylen weiss
 O-Ring- Nitril Kautschuk schwarz
 Sicherungsring-Polypropylen weiss

CABLE

round cable LIYY 2x0,25 mm², grey
 colour of wires: white and brown
 Rundkabel LIYY 2x0,25 mm², grau
 Adernfarben: weiss und braun

MARKING

Production code EN60062/factory code
 Produktionscode EN60062/Fertigungsstätte

float specific density approx. 0,7 g/cm³
 Spezifisches Schwimmergewicht cca. 0,7 g/cm³



Special Product Data	Conditions	Min	Typ	Max	Unit
Contact rating	Any DC combination of V & A not to exceed their individual max.'s			100	W
Switching voltage	DC or Peak AC			350	V
Carry current	DC or Peak AC			1	A
Switching current	DC or Peak AC			0,5	A
Sensor-resistance	measured with 40% overdrive Sensor deactivated			950	mOhm
Housing material		PP			
Case colour		white			
Sealing compound		Polyurethan			

Environmental data	Conditions	Min	Typ	Max	Unit
Operating temperature	cable not moved	-30		80	°C
Operating temperature	cable moved	-5		80	°C
Storage temperature		-30		80	°C
Safety class	DIN EN 60529	IP68			

Cable specification	Conditions	Min	Typ	Max	Unit
Cable type		round cable			
Cable material		PVC			
Cross section		0,25 sq-mm			

General data	Conditions	Min	Typ	Max	Unit
Mounting advice		over 5m cable, a resistor is recommended.			
Tightening torque				0,5	Nm