




| PANDUIT<br>PART NO. * | BUNDLE DIA.     |                 | A             | B             | C             | D             | E             | F             | MIN. LOOP<br>TENSILE lbs.<br>(N) | CROSS<br>SECTION | TIP<br>STYLE | WEIGHT<br>lbs./100 pcs.<br>(g) |
|-----------------------|-----------------|-----------------|---------------|---------------|---------------|---------------|---------------|---------------|----------------------------------|------------------|--------------|--------------------------------|
|                       | MIN. in<br>(mm) | MAX. in<br>(mm) |               |               |               |               |               |               |                                  |                  |              |                                |
| PLT3I                 | .06<br>(1.5)    | 3.00<br>(76)    | .052<br>(1.3) | .145<br>(3.7) | .220<br>(5.6) | .180<br>(4.6) | .260<br>(6.6) | 11.4<br>(290) | 40<br>(178)                      | INTERMEDIATE     | CURVED       | .32<br>(145)                   |
| PLT4I                 | .06<br>(1.5)    | 4.00<br>(102)   | .052<br>(1.3) | .145<br>(3.7) | .220<br>(5.6) | .180<br>(4.6) | .260<br>(6.6) | 14.5<br>(368) | 40<br>(178)                      | INTERMEDIATE     | CURVED       | .40<br>(181)                   |
| PLT1S                 | .06<br>(1.5)    | 1.00<br>(25)    | .052<br>(1.3) | .190<br>(4.8) | .258<br>(6.6) | .220<br>(5.6) | .316<br>(8.0) | 4.8<br>(122)  | 50<br>(222)                      | STANDARD         | CURVED       | .13<br>(58)                    |
| PLT1.5S               | .06<br>(1.5)    | 1.50<br>(38)    | .052<br>(1.3) | .190<br>(4.8) | .258<br>(6.6) | .220<br>(5.6) | .316<br>(8.0) | 6.2<br>(157)  | 50<br>(222)                      | STANDARD         | CURVED       | .26<br>(118)                   |
| PLT2S                 | .06<br>(1.5)    | 1.88<br>(47.8)  | .052<br>(1.3) | .190<br>(4.8) | .258<br>(6.6) | .220<br>(5.6) | .316<br>(8.0) | 7.4<br>(188)  | 50<br>(222)                      | STANDARD         | CURVED       | .29<br>(132)                   |
| PLT2.5S               | .06<br>(1.5)    | 2.50<br>(63.5)  | .052<br>(1.3) | .190<br>(4.8) | .265<br>(6.7) | .220<br>(5.6) | .337<br>(8.6) | 9.8<br>(249)  | 50<br>(222)                      | STANDARD         | CURVED       | .38<br>(173)                   |
| PLT3S                 | .06<br>(1.5)    | 3.00<br>(76)    | .052<br>(1.3) | .190<br>(4.8) | .265<br>(6.7) | .220<br>(5.6) | .337<br>(8.6) | 11.5<br>(292) | 50<br>(222)                      | STANDARD         | CURVED       | .45<br>(204)                   |

**NOTES:**

- 1) RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.  
 \*2) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE & PART COLOR.

SS\_5540\_00.PRT

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

PAN-TY CABLE TIES  
PLT SERIES

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ± .005 (.127) (XXX) ± .020 (.51)  
(.XX) ± .02 (.51) ANGLES ± .005

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY  
CEW

MAT'L:

SCALE  
NONEDATE  
12-27-84

NYLON 6/6

DRAWING NO.  
SS-5540  
SHEET 2

DWG  
A  
SIZE

| 28  | 9/2/03 | JABO |     | ADDED C REF. DIMENSION TO TIE.<br>C DIM. WAS ALREADY IN MATRIX | 5540 | 28 |      |     |  |
|-----|--------|------|-----|----------------------------------------------------------------|------|----|------|-----|--|
| REV | DATE   | BY   | CHK | DESCRIPTION                                                    | ECN  | R  | CUST | SUP |  |