


Small Signal Transistors

TO-92HS Case


$P_D(@T_C=25^{\circ}\text{C})=1.0\text{Watt}$



TYPE NO.	POLARITY	V _{CB0}	V _{CEO}	V _{EBO}	I _{CBO} @ V _{CB0}		h _{FE}		I _C	@ V _{CE}	V _{CE(SAT)} @ I _C		C _{ob}	f _T	NF	LEAD CODE
		(V)	(V)	(V)	(nA)	(V)			(mA)	(V)	(V)	(mA)	(pF)	(MHz)	(dB)	
		MIN	MIN	MIN	MAX		MIN	MAX			MAX		MAX	MIN	MAX	
2N3402	NPN	25	25	5.0	100	25	75	225	2.0	4.5	0.3	50	---	---	---	ECB
2N3403	NPN	25	25	5.0	100	25	180	540	2.0	4.5	0.3	50	---	---	---	ECB
2N3404	NPN	50	50	5.0	100	50	75	225	2.0	4.5	0.3	50	---	---	---	ECB
2N3405	NPN	50	50	5.0	100	50	180	540	2.0	4.5	0.3	50	---	---	---	ECB
2N4425	NPN	60	40	5.0	30	40	180	540	2.0	4.5	0.3	50	---	---	---	ECB
HS3402	NPN	25	25	5.0	100	25	75	225	2.0	4.5	0.3	50	---	---	---	EBC
HS3403	NPN	25	25	5.0	100	25	180	540	2.0	4.5	0.3	50	---	---	---	EBC
HS3404	NPN	50	50	5.0	100	50	75	225	2.0	4.5	0.3	50	---	---	---	EBC
HS3405	NPN	50	50	5.0	100	50	180	540	2.0	4.5	0.3	50	---	---	---	EBC
HS5306	NPN	25	25	12	100	25	7,000	70,000	2.0	5.0	1.4	200	10	60	---	ECB
HS5306A	NPN	25	25	12	100	25	7,000	70,000	2.0	5.0	1.4	200	10	60	10	ECB
HS5308	NPN	40	40	12	100	40	7,000	70,000	2.0	5.0	1.4	200	10	60	---	ECB
HS5308A	NPN	40	40	12	100	40	7,000	70,000	2.0	5.0	1.4	200	10	60	10	ECB
GES5810-J1	NPN	35	25	5.0	100	25	60	200	2.0	2.0	0.75	500	15	100	---	EBC
GES5811-J1	PNP	35	25	5.0	100	25	60	200	2.0	2.0	0.75	500	15	100	---	EBC
GES5812-J1	NPN	35	25	5.0	100	25	150	500	2.0	2.0	0.75	500	15	135	---	EBC
GES5813-J1	PNP	35	25	5.0	100	25	150	500	2.0	2.0	0.75	500	15	135	---	EBC
GES5814-J1	NPN	50	40	5.0	100	25	60	160	2.0	2.0	0.75	500	15	100	---	EBC
GES5815-J1	PNP	50	40	5.0	100	25	60	160	2.0	2.0	0.75	500	15	100	---	EBC
GES5816-J1	NPN	50	40	5.0	100	25	100	200	2.0	2.0	0.75	500	15	120	---	EBC
GES5817-J1	PNP	50	40	5.0	100	25	200	200	2.0	2.0	0.75	500	15	120	---	EBC
GES5818-J1	NPN	50	40	5.0	100	25	150	300	2.0	2.0	0.75	500	15	135	---	EBC
GES5819-J1	PNP	50	40	5.0	100	25	150	300	2.0	2.0	0.75	500	15	135	---	EBC
GES5820-J1	NPN	70	60	5.0	100	25	60	160	2.0	2.0	0.75	500	15	100	---	EBC
GES5821-J1	PNP	70	60	5.0	100	25	60	160	2.0	2.0	0.75	500	15	100	---	EBC
GES5822-J1	NPN	70	60	5.0	100	25	100	200	2.0	2.0	0.75	500	15	120	---	EBC
GES5823-J1	PNP	70	60	5.0	100	25	100	200	2.0	2.0	0.75	500	15	120	---	EBC
GES6010-J1	NPN	50	40	5.0	10	25	100	300	10	1.0	0.5	500	10	105	5.0	EBC
GES6011-J1	PNP	50	40	5.0	10	25	100	300	10	1.0	0.75	500	15	75	3.0	EBC
GES6012-J1	NPN	50	40	5.0	10	25	200	500	10	1.0	0.5	500	10	135	3.0	EBC
GES6013-J1	PNP	50	40	5.0	10	25	200	500	10	1.0	0.75	500	15	100	2.0	EBC
GES6014-J1	NPN	70	60	5.0	10	25	100	300	10	1.0	0.5	500	10	105	5.0	EBC
GES6015-J1	PNP	70	60	5.0	10	25	100	300	10	1.0	0.75	500	15	75	3.0	EBC
GES6016-J1	NPN	70	60	5.0	10	25	200	500	10	1.0	0.5	500	10	135	3.0	EBC
GES6017-J1	PNP	70	60	5.0	10	25	200	500	10	1.0	0.75	500	15	100	2.0	EBC
GES6218-J1	NPN	300	300	5.0	500	250	20	---	20	10	1.0	10	5.0	50	---	EBC
GES6219-J1	NPN	250	250	5.0	1,000	200	20	---	20	10	1.0	10	5.0	50	---	EBC
GES6220-J1	NPN	200	200	5.0	1,000	150	20	---	20	10	2.0	20	5.0	50	---	EBC
GES6221-J1	NPN	150	150	5.0	10,000	100	20	---	20	10	2.3	20	5.0	50	---	EBC

NOTE: Most devices are available in CBE lead code on special order.
Shaded areas indicate Darlington.

TO-92HS Mechanical Drawing



All dimensions in inches (mm).

LEAD CODEPIN

	<u>1</u>	<u>2</u>	<u>3</u>
EBC	E	B	C
ECB	E	C	B
CBE	C	B	E