





MARKETING SALES DRAWING

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []




MOUNTING HARDWARE



NOTES:

1. TUSONIX STANDARD PART NUMBER: 4400-000.
TUSONIX RoHS COMPLIANT PART NUMBER: 4400-000 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. LEAD, BUSHING, AND MOUNTING HARDWARE: SILVER PLATED.
3. PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS. STANDARD PART: BLACK INK. RoHS PART: GREEN INK.
4. OPERATING TEMPERATURE RANGE : -55°C TO +125°C.
5. MAX. RECOMMENDED SOLDERING TEMPERATURE: 260°C.
6. SUPPLIED WITH HEX NUT AND INTERNAL TOOTH LOCK WASHER.
7. MAX. RECOMMENDED MOUNTING TORQUE - 2.0 lb.-in. [.226 Nm].

100		GMV		300	200	10 G Ω	500	10	----	----	3	20	28
CAP.(pf)		TOLERANCE		85°C	125°C	I.R. MIN. @ 100 (VDC.)	DWV (VDC)	DC CURRENT (AMPS)	1 MHz	10 MHz	100 MHz	1 GHz	10 GHz
				DC WORKING VOLTAGE					MIN. NO LOAD INSERTION LOSS (dB) @ 25°C PER MIL-STD-220				
REVISION RECORD Original Release C.O. 0 REDRAWN & REVISED ADDED 008,009. E.C. 05-30-90 5261 VARS 005,006,007 & 1MHz COLUMN ADDED. L.E. 11-07-90 5591 RDN TO COMP FMT & ADDED METRIC. S.M. 11-08-01 20000926-3-01 REVISED DWG. DRAWING MADE FOR EACH VAR. S.M. 12-02-02 20021125-1-01 10 (AMPS) WAS 5 (AMPS) L.E. 06-23-04 20040621-1-01 ADDED & REVISED NOTES. S.M. 12-14-05 20051122-2-02 --TOLERANCES-- Unless Otherwise Specified DECIMAL ± NOTED ANGLES ±  TUSONIX TUCSON, ARIZONA Title BUSHING STYLE EMI FILTER Drawn S.M. 11-07-01 Scale 5 X Approved B.Mc 11-07-01 A 4400-000													