

- Bifurcated contacts for low resistance and high reliability – suitable for switching low-level electronic currents
- Double-break contacts with electrically separate NO and NC circuits in conformity with VDE 0660 part 206
- 10A 500VAC/600VDC rated
- Turret head position rotatable in 90° increments
- Centre-position indicator arrow – lever actuators
- Wide range of actuators
- Single and dual cable entry models
- Removable contact block for ease of wiring
- Metal or plastic housing options
- IP65 according to BS EN 60947-1
- FM and FR dimensions in accordance with EN50047 with dual fixing centres: 20 and 22mm
- UL and CUL approved



FM		5		01		7	
Compact metal housing	FM					-	Standard turret without reset button
Compact plastic housing	FR					7	With reset button
Dual-entry metal housing	FZ					71	Early trip point with reset button
Dual-entry plastic housing	FX						
Snap-action contacts, 1NO + 1NC		5		-	Standard actuators - see following pages for type options		
Slow-action, break before make 1NO + 1NC		6		38	Lift style turret specify lever type for lift-style switches		
Slow-action, make before break 1NO + 1NC		7		VFL313	Fixed position roller		
Slow-action contacts, 2NC		9		VFL353	Single adjustment roller		
Slow-action contacts, 2NO		10		VFL354	Dual adjustment roller		
Snap-action contacts, 2NC		11					
Slow-action contacts, break before make 2NC + 1NO		20					
Slow-action contacts, 3NC		21					
Slow-action contacts, break before make 1NC + 2NO		22					
Snap-action contacts, 2NO + 2NC		2					

Please note: Positive break applies to the NC contacts of types 5, 6, 7, 9, 11, 20, 21 and 22 only.

Please note: Positive break applies to the NC contacts of types 5, 6, 7, 9, 11, 20, 21 and 22 only.

BS/EN 60947-5-1		
AC15 – Control of AC electromagnetic loads > 72VA sealed – replaces AC11	230VAC	6A
	400VAC	4A
	500VAC	1A
DC13 – Control of DC electromagnetic loads where the time taken to reach 95% of the rated current is equal to 6 times the power of the load (where P ≤ 50W) – replaces DC11	24VDC	6A
	125VDC	1.1A
	250VDC	0.4A

Standard contacts: NO: 13–14 NC: 21–22
Terminal screws: M3.5 with rising cable clamps.

Note: The positive break of the type 5 contact block applies to the NC contacts only. Connections to safety circuits should NOT be made using the NO contacts.

To ensure positive breaking of the contacts, exceed the pre-travel by 1.5mm or 25° according to the model. Maximum screw tightening torque 0.8Nm (8Kacm)

IMO

Rated thermal current I _{th}	10A
Rated working voltage	500VAC/600VDC
Maximum operating frequency	6000/hour
Mechanical life	>20 million operations
Contact form	1NO + 1NC
Initial contact resistance	<25 mΩms
Contact gap	>2.5mm (2 x 1.25mm conforming to VDE 0660 part 206)
Contact material	silver
Dielectric strength	2000VAC, 50/60Hz for 1 minute between open contacts 2000VAC, 50/60Hz for 1 minute between current-carrying parts and ground
Protection rating	IP65
Ambient operating temperature	−25 to +80 deg. C
Ambient humidity	95% R.H.
Maximum wire size	2 x 1.5mm ² flexible, 2 x 2.5mm ² solid
Housing material	FM/FZ: die-cast metal alloy, FR/FX: self-extinguishing, glass-reinforced, thermoplastic resin
Conduit entry	PG 13.5

Technical drawing of the PG 13 pump assembly, showing front and side views with dimensions in millimeters.

Front View Dimensions:



- Total height: 73
- Height from base to mounting flange: 52
- Height of mounting flange: 21
- Distance from base to center of mounting holes: 3
- Distance between mounting holes: 8
- Distance between mounting holes (center-to-center): 8
- Distance between mounting holes (edge-to-edge): 2 x 7
- Distance between mounting holes (edge-to-center): 2
- Distance between mounting holes (center-to-center): 22
- Distance between mounting holes (edge-to-center): 20
- Base width: 30
- Base width (edge-to-center): 8

Side View Dimensions:

- Total height: 12
- Height of mounting flange: 2
- Distance between mounting holes (center-to-center): 24
- Base width: 30
- Base width (edge-to-center): 8

Labels:



- PG 13 5



One-way roller – side actual

OF	615g
PT	2.9mm
OT	5.6mm
MD	1.6mm
OP	—
OS	1m/s using a 30° cam

Note: plastic roller only




Also available: Actuator type 10. Piston plunger with M12 mounting bush on the turret. Characteristics as for type 08 except: OP=34mm.

Compact Heavy Duty Limit Switches

FM/FR/FZ/FX continued


IMO

Standard actuator options – FM and FR series continued



Actuator type 14
Mushroom head plunger (red plastic)


OF	820g
PT	2mm
OT	4mm
MD	1mm
OP	26mm
OS	0.5m/s



Actuator type 15
Roller piston plunger

OF	820g
PT	2mm
OT	4mm
MD	1mm
OP	29mm
OS	0.3m/s using a 30° cam


Notes: FM515 ø 12mm metal roller as standard,
FR515 ø 11mm plastic roller as standard.
For FR with ø 12mm metal roller: FR5151



Actuator type 20
Sealed coil spring with flexible rod

OF	100g at 73 the length of the actuator
PT	18°
OT	—
MD	10°
OP	—
OS	1m/s


Notes: Not suitable for safety circuits.
Not suitable for use with contact blocks 20, 21 or 22



Actuator type 21
Sealed coil spring with cat's whisker

OF	70g at 73 the length of the actuator.
PT	18°
OT	—
MD	10°
OP	—
OS	1m/s


Notes: Not suitable for safety circuits
Not suitable for use with contact blocks 20, 21 or 22



Actuator type 25
Sealed coil spring

OF	185g at 73 the length of the actuator
PT	18°
OT	—
MD	10°
OP	—
OS	1m/s


Notes: Not suitable for safety circuits
Not suitable for use with contact blocks 20, 21 or 22



Actuator type 31
Roller-lever

OF	1000gcm
PT	30°
OT	45°
MD	13°
OP	—
OS	1.5m/s using a 30° cam

Notes: 1. ø18mm plastic roller as standard, ø20mm metal roller actuator part no.: 311.
2. Lever position adjustable over 360° in 10° increments.




Actuator type 50
Adjustable steel rod

OF	1000gcm
PT	30°
OT	45°
MD	13°
OP	—
OS	1.5m/s

Note: Lever position adjustable over 360° in 10° increments.

Also available: Actuator type 69. Adjustable glass-fibre rod ø6x200mm. Characteristics as for type 50, but not suitable for safety circuits.



Actuator type 51
Roller-lever with large offset


OF	1000gcm
PT	30°
OT	45°
MD	13°
OP	—
OS	1.5m/s using a 30° cam

Notes: 1. Plastic roller as standard, metal roller actuator part no.: 511. 2. Lever position adjustable over 360° in 10° increments.

Compact Heavy Duty Limit Switches FM/FR/FZ/FX continued




Standard actuator options – FM and FR series continued



Actuator type 53
Porcelain roller-lever

OF 615gcm
PT 30°
OT 45°
MD 13°
OP –
OS –


Note: Lever position adjustable over 360° in 10° increments.



Actuator type 54
Roller-lever with small offset

OF 1000gcm
PT 30°
OT 45°
MD 13°
OP –
OS –

Notes: 1. Plastic roller as standard, metal roller actuator part no.: 541. 2. Lever position adjustable over 360° in 10° increments.




Actuator type 55
Adjustable roller-lever

OF 1000gcm
PT 30°
OT 45°
MD 13°
OP –
OS –


Notes: 1. Plastic roller as standard, metal roller actuator part no.: 551. 2. Lever position adjustable over 360° in 10° increments.

Standard actuator options – FZ and FX series



Actuator type 01
Piston plunger


OF 820g
PT 2mm
OT 4mm
MD 1mm
OP 19mm
OS 0.5m/s



Actuator type 02
One-way roller – top actuated

OF 615g
PT 2.9mm
OT 5.6mm
MD 1.6mm
OP 36.1mm
OS 1m/s using a 30° cam


Note: plastic roller only



Actuator type 05
One-way roller – side actuated

OF 615g
PT 2.9mm
OT 5.6mm
MD 1.6mm
OP –
OS 1m/s using a 30° cam


Note: plastic roller only



Actuator type 07
One-way roller adjustable
3 positions top actuated
3 positions side actuated

OF 410g
PT 5mm
OT 8mm
MD 2.8mm
OP 47mm
OS 1m/s using a 30° cam

Note: Plastic roller only radius: pivot to centre of roller = 28mm



Actuator type 08
Sealed piston plunger


OF 820g
PT 2mm
OT 4mm
MD 1mm
OP 30mm
OS 0.5m/s

Compact Heavy Duty Limit Switches

FM/FR/FZ/FX continued


IMO

Standard actuator options – FZ and FX series continued




Actuator type 15 Roller piston plunger

OF 820g
PT 2mm
OT 4mm
MD 1mm
OP 29mm
OS 0.3m/s using a 30° cam
Note: FZ515 ø12mm metal roller as standard.
Note: FX515 ø11mm plastic roller as standard.
Note: For FX with ø12mm metal roller: FX5151




Actuator type 20 Sealed coil spring with flexible rod

OF 100g at 2/3 the length of the actuator
PT 18°
OT –
MD 10°
OP –
OS 1m/s
Notes: Not suitable for safety circuits
Not suitable for use with contact blocks 20, 21 or 22




Actuator type 21 Sealed coil spring with cat's whisker

OF 70g at 2/3 the length of the actuator
PT 18°
OT –
MD 10°
OP –
OS 1m/s
Notes: Not suitable for safety circuits
Not suitable for use with contact blocks 20, 21 or 22




Actuator type 25 Sealed coil spring

OF 185g at 2/3 the length of the actuator
PT 18°
OT –
MD 10°
OP –
OS 1m/s
Notes: Not suitable for safety circuits
Not suitable for use with contact blocks 20, 21 or 22




Actuator type 31 Roller-lever

OF 1000gcm
PT 30°
OT 45°
MD 13°
OP –
OS 1.5m/s using a 30° cam
Notes: 1. ø18mm plastic roller as standard, ø20mm metal roller actuator part no.: 311
2. Lever position adjustable over 360° in 10° increments.




Actuator type 50 Adjustable steel rod

OF 1000gcm
PT 30°
OT 45°
MD 13°
OP –
OS 1.5m/s
Note: Lever position adjustable over 360° in 10° increments.



Actuator type 51 Roller-lever with large offset

OF 1000gcm
PT 30°
OT 45°
MD 13°
OP –
OS 1.5m/s using a 30° cam
Notes: 1. Plastic roller as standard, metal roller actuator part no.: 511. 2. Lever position adjustable over 360° in 10° increments.




Actuator type 53 Porcelain roller-lever

OF 615gcm
PT 30°
OT 45°
MD 13°
OP –
OS –
Note: Lever position adjustable over 360° in 10° increments.

Compact Heavy Duty Limit Switches FM/FR/FZ/FX continued

IMO

Standard actuator options – FZ and FX series continued




Actuator type 54

Roller-lever with small offset

OF 1000gcm
PT 30°
OT 45°
MD 13°
OP –
OS 1.5m/s using a 30° cam

Notes: 1. Plastic roller as standard, metal roller actuator part no.: 541. 2. Lever position adjustable over 360° in 10° increments.




Actuator type 55

Adjustable roller-lever

OF 1000gcm
PT 30°
OT 45°
MD 13°
OP –
OS 1.5m/s using a 30° cam

Notes: 1. Plastic roller as standard, metal roller actuator part no.: 551. 2. Lever position adjustable over 360° in 10° increments.



Actuator type 69

Adjustable glass-fibre rod


OF 1000gcm
PT 30°
OT 45°
MD 13°
OP –
OS 1.5m/s

Notes: 1. Not suitable for safety circuits 2. Lever position adjustable over 360° in 10° increments.

Standard switches with reset buttons

Examples – many other types available – for reset button, add suffix – 7 to standard part numbers


Operation – once contacts have changed-over and latched, the reset button must be operated for the contacts to change back



FR 501-7

Piston plunger


Pre-travel 2mm
Additional travel beyond the operating point until the mechanism latches 2mm



FR 502-7

One-way roller – top actuated


Pre-travel 2.9mm
Additional travel beyond the operating point until the mechanism latches 2.3mm



FR 515-7

Roller piston plunger


Pre-travel 2mm
Additional travel beyond the operating point until the mechanism latches 2mm



FR 530-7

Roller-lever


Pre-travel 30°
Additional travel beyond the operating point until the mechanism latches 25°



FR 507-7

One-way roller – adjustable

3 positions top actuated
3 positions side actuated
Pre-travel 5mm
Additional travel beyond the operating point until the mechanism latches 3.4mm



FX 515-7

Roller piston plunger

Pre-travel 2mm
Additional travel beyond the operating point until the mechanism latches 2mm

www.imopc.com

Compact Heavy Duty Limit Switches

FM/FR/FZ/FX continued




Replacement contact blocks

B5	1NO + 1NC	Positive break	
		<i>Snap action</i> standard contact block	
B6	1NO + 1NC	Positive break	
		<i>Slow action</i> break before make	
B7	1NO + 1NC	Positive break	
		<i>Slow action</i> make before break	
B9	2NC	Positive break	
		<i>Slow action</i> , contacts 11-12, 21-22 open at the same time	
B14		Positive break	
		<i>Slow action</i> , contacts 11-12 open first, further actuator travel causes contacts 21-22 to open	
B10	2NO	<i>Slow action</i> , contacts 13-14, 23-24 close at the same time	
B15		<i>Slow action</i> , contacts 13-14 close first, further actuator travel causes contacts 23-24 to close	
B2	2NO + 2NC	<i>Snap action, double pole</i>	

Plug and socket limit switches

All FR/FM/FZ/FX series limit switches can be converted to a plug-in style by the addition of an adaptor.

Part number
8R4D26E03C3003



The adaptor is screwed into the limit switch and the four flying leads connected to the four terminals of the contact block.

Suitable 4-wire plug leads are available.

Ratings 250VAC/300VDC

3A

IP67

Cable glands

Cable glands are available to enable standard multi-core cables to be connected without the use of conduit.

Two sizes are possible:

Part number **VFPG13.5** Cable size $\varnothing$ 9-12mm

Part number **VFPG13.5/6** Cable size $\varnothing$ 6-9mm

