

## FLK 40/4X14/EZ-DR/ 200/OB32

Order No.: 2298522



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2298522>

Round cable set, for connection to Allen Bradley SLC 500, OB 32 and IB 32, with one 40-position socket strip and four 14-position socket strips, for splitting 32 channels into 4x8 channels, for OB 32, no. of positions 40/4x14, cable length 2.0 m

### Commercial data

|                          |                                                                                                        |
|--------------------------|--------------------------------------------------------------------------------------------------------|
| GTIN (EAN)               | <br>4 017918 612412 |
| Note                     | Made-to-order                                                                                          |
| sales group              | I680                                                                                                   |
| Pack                     | 1 pcs.                                                                                                 |
| Customs tariff           | 85444290                                                                                               |
| Catalog page information | Page 194 (IF-2009)                                                                                     |

### Product notes

WEEE/RoHS-compliant since:  
03/13/2006



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

### Technical data

#### General

|                                         |           |
|-----------------------------------------|-----------|
| Nominal voltage $U_N$                   | < 50 V AC |
|                                         | 60 V DC   |
| Max. current carrying capacity per path | 1 A       |

|                                               |                                                     |
|-----------------------------------------------|-----------------------------------------------------|
| Max. conductor resistance                     | 0.16 $\Omega$ /m                                    |
| Ambient temperature (operation)               | -20 °C ... 50 °C                                    |
| Ambient temperature (storage/transport)       | -20 °C ... 70 °C                                    |
| Number of positions, control side             | 40                                                  |
| Number of connectors, control side            | 1                                                   |
| Number of positions, module side              | 14                                                  |
| Number of connectors, modul side              | 4                                                   |
| Fixed cable length                            | 2 m                                                 |
| Single wire, cross section                    | 0.14 mm <sup>2</sup>                                |
| AWG                                           | 26                                                  |
| Conductor construction: Number of litz wires: | 7                                                   |
| Single wire, material                         | Cu tin-plated                                       |
| External diameter                             | 7.8 mm                                              |
| Cable, preassembly                            | Insulation displacement, IEC 60352-4/DIN EN 60352-4 |
| Shielding                                     | no                                                  |

#### Certificates / Approvals



Certification

GOST

**Address**

PHOENIX CONTACT Deutschland GmbH  
Flachsmarktstr. 8  
32825 Blomberg, Germany  
Phone +49 5235 3 12000  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.de>



© 2011 Phoenix Contact  
Technical modifications reserved;