

N-Series 800

Following the recent success of its N-Series 500 and 600, Erem now introduces the 812N and 822N side cutters. These two models are part of the well-known Erem "Magic" line, i.e. highest quality machined tool steel, integrated unbreakable springs, constant spring force, limited handle opening, no blade overlapping, static dissipative, soft grips which are easy to replace.

RS 431-0121



Erem 812N


Semi flush cut for large wires.
Max. cutting capacity: Cu 1,8 mm (.070)

RS 431-0424



Erem 822N

Nice full flush cut, reduces effort. For soft wires only.
Max. cutting capacity: Cu 1,8 mm (.070)



A	Blade length:	15 mm / .591
B	Head width:	13,5 mm / .530
C	Thickness:	11 mm / .433
L	Total length:	120 mm / 4 3/4"



AIRETOOL®
APEX® • BUCKEYE®
CAMPBELL® • CLECO®
COOPER AUTOMATION™ • CRESCENT®
DGD® • DOLER® • DOTCO® • EREM®
GARDNER-DENVER® • GARDOTRANS™
GETA™ • KAHNETICS® • LUFKIN®
MASTER POWER® • METRONIX™
NICHOLSON® • PLUMB® • H.K. PORTER®
QUACKENBUSH™ • RECOULES™ • ROTOR™
UTICA® • WELLER® • WIRE-WRAP®
WISS® • XCELITE®