

Ultra Fast Switching Rectifier 3A



Features:

- Fast reverse recovery time, t_{rr}
- Low forward voltage, V_F
- Low cost axial packages
- Void-free plastic in DO-201AD package
- 3A operation at $T_A = 55^\circ\text{C}$ with no thermal runaway
- Exceeds environmental standards of MIL-S-19500/228
- Ultra fast switching for high efficiency

Mechanical Data:

Case	: Moulded plastic
Terminals	: Axial leads, solderable per MIL-STD-202 Method 208
Polarity	: Band denotes cathode
Mounting Position	: Any

Maximum Ratings and Electrical Characteristics:

Ratings at 25°C ambient temperature unless otherwise specified.

Resistive or inductive load, 60Hz.

Parameters	UF304	Units
Peak reverse voltage, repetitive; V_{RM}	400	V
Maximum RMS voltage	280	
DC blocking voltage; V_R	400	
Average forward current, I_o at $T_A = 55^\circ\text{C}$ 3.8" Lead length, 60Hz, resistive or inductive load	3	A
Peak forward surge current I_{FM} (surge) 8.3m seconds Single half sine-wave superimposed on rated load (JEDEC method)	150	
Maximum forward voltage V_F at 3A, 25°C	1.1	V
Maximum reverse current at rated $T_J = 25^\circ\text{C}$ Reverse Voltage $T_J = 100^\circ\text{C}$	10 500	mA
Typical junction capacitance (Note 1) C_J	75	pF
Typical junction resistance (Note 2) $R_{\theta JA}$	20	$^\circ\text{C/W}$
Reverse recovery time $I_F = 0.5\text{A}$, $I_R = 1\text{A}$, $I_{rr} = 0.25\text{A}$	50	ns
Operating and storage temperature range	-55 to +150	$^\circ\text{C}$


Notes:

1. Measured at 1MHz and applied reverse voltage of 4V DC.
2. Thermal resistance from junction to ambient and from junction to lead length 0.375" (9.5mm) PCB mounted.

Ultra Fast Switching Rectifier 3A



Rating and Characteristics Curves



Note:

1. Rise Time = 7ns maximum
Input Impedance = 1MΩ, 22pF
2. Rise Time = 10ns maximum
Source Impedance = 50Ω




Figure 1 - Reverse Recovery Time Characteristics and Test Circuit Diagram




Figure 2 - Forward Characteristics




Figure 3- Forward Current Derating Curve

Ultra Fast Switching Rectifier 3A




Figure 4 - Typical Reverse Leakage Characteristics





Figure 5 - Peak Forward Surge Current

Dimensions

DO-201AD



Dimensions: Inches (Millimetres)

Part Number Table

Description	Part Number
Diode, Ultrafast, 3A, 400V	UF304

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.