ALUMINUM ELECTROLYTIC CAPACITORS

nichicon

FW Standard, For Audio Equipment series

● Compliant to the RoHS directive (2011/65/EU).





■Specifications

Item	Performance Characteristics
Category Temperature Range	−40 to +85°C
Rated Voltage Range	6.3 to 100V
Rated Capacitance Range	0.1 to 33000μF
Capacitance Tolerance	±20% at 120Hz, 20°C
Leakage Current	After 1 minute's application of rated voltage at 20°C, leakage current is not more than 0.03 CV or 4 (μA) , whichever is greater. After 2 minutes' application of rated voltage at 20°C, leakage current is not more than 0.01 CV or 3 (μA) , whichever is greater.
Tangent of loss angle (tan δ)	Measurement frequency : 120Hz at 20°C For capacitance of more than 1000μF, add 0.02 for every increase of 1000μF.
Stability at Low Temperature	Measurement frequency : 120Hz
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 2000 hours at 85°C.
Shelf Life	After storing the capacitors under no load at 85°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.
Marking	Printed with black color letter on Gold sleeve.

Rated voltage (V)	6.3	10	16	25	35	50	63	100
tan δ (MAX.)	0.28	0.24	0.20	0.16	0.14	0.12	0.10	0.08

Rated voltage (V)		6.3	10	16	25	35	50	63	100
Impedance ratio ZT / Z20 (MAX.)	Z−25°C / Z+20°C	5	4	3	2	2	2	2	2
	Z−40°C / Z+20°C	12	10	8	5	4	3	3	3

Capacitance change	Within ±20% of the initial capacitance value
tan δ	200% or less than the initial specified value
Leakage current	Less than or equal to the initial specified value

■Radial Lead Type



(mm)

φD	5	6.3	8	10	12.5	16	18	20	22	25
P	2.0	2.5	3.5	5.0	5.0	7.5	7.5	10	10	12.5
φd	0.5	0.5	0.6	0.6	0.6	0.8	0.8	1.0	1.0	1.0
β	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	1.0	1.0

α	
	(φD < 20) 1.5
	(φD ≧ 20) 2.0

Type numbering system (Example : 10V 1000μF)

1	2	3	4	5	6	7	8	9	10	11
U	F	W	1	A	1	0	2	M	P	D

- Configuration ※
- Capacitance tolerance (±20%)
- Rated capacitance (1000μF)
- Rated voltage (10V)
- Series name
- Type

※Configuration

φ D	Pb-free leadwire Pb-free PET sleeve
5	DD
6.3	ED
8 ·10	PD
12.5 to 18	HD
20 to 25	RD

• Please refer to page 20 about the end seal configuration.

Please refer to page 20, 21, 22 about the formed or taped product spec.
Please refer to page 4 for the minimum order quantity.

●Dimension table in next page.

FW series

■Dimensions

Cap.(μF) \ V	6.3		10		16		25		35		50		63		100	
Code	0J		1A		1C		1E		1V		1H		1J		2A	
0.1	0R1										5×11	1.1			5×11	2.1
0.22	R22										5×11	2.4			5×11	4.7
0.33	R33										5×11	3.5			5×11	7.0
0.47	R47										5×11	5.0			5×11	10
1	010										5×11	10			5×11	21
2.2	2R2										5×11	23			5×11	30
3.3	3R3										5×11	35			5×11	40
4.7	4R7										5×11	40			5×11	45
10	100										5×11	65	5×11	70	6.3×11	75
22	220										5×11	95	5×11	100	6.3×11	120
33	330								5×11	105	5×11	120	6.3×11	140	8×11.5	160
47	470						5×11	115	5×11	120	6.3×11	150	6.3×11	165	10×12.5	210
100	101		5×11	145	5×11	155	6.3×11	185	6.3×11	200	8×11.5	250	10×12.5	300	10×20	350
220	221		6.3×11	230	6.3×11	250	8×11.5	320	10×12.5	370	10×12.5	410	10×16	470	12.5×25	600
330	331	6.3×11	6.3×11	270	8×11.5	360	10×12.5	420	10×12.5	470	10×16	570	10×20	650	12.5×25	750
470	471	6.3×11	6.3×11	330	8×11.5	420	10×12.5	530	10×16	630	12.5×20	760	12.5×20	880	16×25	1000
1000	102	8×11.5	10×12.5	630	10×16	770	10×20	950	12.5×20	1100	12.5×25	1300	16×25	1300	18×40	1370
2200	222	10×20	10×20	1050	12.5×20	1250	12.5×25	1550	16×25	1800	16×35.5	2090	18×35.5	2200	22×50	2400
3300	332	10×20	12.5×20	1420	12.5×25	1700	16×25	1950	16×35.5	2220	18×35.5	2360	20×40	2700	25×50	2900
4700	472	12.5×20	12.5×25	1800	16×25	2100	16×31.5	2360	18×35.5	2490	20×40	2900	22×50	3400		
6800	682	12.5×25	16×25	2150	16×35.5	2500	18×35.5	2590	20×40	3000	22×50	3500	25×50	3500		
10000	103	16×25	16×35.5	2500	18×35.5	2640	20×40	3000	22×50	3700	25×50	4000				
15000	153	16×35.5	18×35.5	2720	20×40	3400	22×50	3800	25×50	4300						
22000	223	18×40	20×40	3700	22×50	4200	25×50	4500								
33000	333	22×50	22×50	4500	25×50	4800									Case size φD×L (mm)	Rated ripple

Rated ripple current (mArms) at 85°C 120Hz

● Frequency coefficient of rated ripple current

Cap.(μF) \ Frequency	50Hz	120Hz	300Hz	1kHz	10kHz or more
0.1 to 47	0.75	1.00	1.35	1.57	2.00
100 to 470	0.80	1.00	1.23	1.34	1.50
1000 to 33000	0.85	1.00	1.10	1.13	1.15