




PRODUCT NUMBER	NO. OF MODULES	NO. OF POSITIONS	DIM A	LOADING CONFIGURATION
10022898-X001	2	60	23.95	FULLY LOADED
10022898-X002	3	90	35.95	
10022898-X003	6	180	71.95	
10022898-X004	8	240	95.95	
10022898-X005	1	30	11.95	
10022898-X001LF	2	60	23.95	
10022898-X002LF	3	90	35.95	
10022898-X003LF	6	180	71.95	
10022898-X004LF	8	240	95.95	
10022898-X005LF	1	30	11.95	


0 +0.40
-0.10
RELATIVE TO SURFACE T



NOTES:

- CONNECTOR MATERIALS:
HOUSING: LCP, 30% GLASS FILLED,
UL 94-V0 COMPLIANT
TERMINAL: PHOSPHOR BRONZE ALLOY
- PLATING ON TAIL:
PRESS-FIT TYPE
10022898-XXXX IS 0.5-1.5um SnPb
10022898-XXXXLF IS 0.5-1.5um Sn (LEAD FREE)
- PRODUCT SPECIFICATION:
GS-12-002

- APPLICATION SPECIFICATIONS:
BUS-20-061
GS-20-001
TA-941




NOTES:

- PRODUCT MARKING: (PART NUMBER & LOT CODE).
- INDICATED HOLES ARE UNPLATED.
- DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT.
- TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD.
- DIMENSION APPLIES TO BOTH PRESS-FIT AND SOLDER TAIL TERMINATIONS.
- THESE PRODUCTS WHERE THE PART NUMBER ENDS IN "LF" MEET THE EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

ALL PRODUCTS MANUFACTURED BEFORE SEPTEMBER 2005 WILL WITHSTAND EXPOSURE TO 240°C FOR 60 SECONDS IN A CONVECTION, INFAR-RED OR VAPOR PHASE REFLOW OVEN.

ALL PRODUCTS MANUFACTURED AFTER AUGUST 2005 WILL WITHSTAND EXPOSURE TO 260°C FOR 60 SECONDS IN A CONVECTION, INFAR-RED OR VAPOR PHASE REFLOW OVEN.

- FOR LEAD FREE PART NUMBERS ADD "LF" SUFFIX. EXAMPLE: 10022898-XXXXLF.




SEE TABLE 1

RECOMMENDED PC BOARD LAYOUT,
COMPONENT SIDE.

TABLE 1	
PLATED THRU HOLE REQUIREMENTS	
HOLE DIAMETER AFTER PLATING	0.65-0.80
DRILLED HOLE	0.81-0.86 (0.85 DRILL)
COPPER PLATING	0.025 - 0.05
SnPb PLATING	0.005-0.015

SEE DRAWING 58351
FOR OTHER OPTIONS



mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI	
NOTE 1									
ltr	ecn no	dr	date	linear	.X±.3	projection		title	
A	V03-0181	TAB	2/12/03		.XX±.13			B SERIES R/A SIGNAL RECEPT ASSY,	
B	V03-0277	TAB	3/06/03		.XXX±.051			5 ROW, PF, SPECAIL PLATING	
C	V06-0124	JRV	3/20/06	angles	0°±2°			product family METRAL (tm)	code
D	DG07-0171	Cenh	05/25/07	dr	T. BRUNGARD	2/12/03	MM	size	213
E	DG08-0171	TER	8/26/08	enrg	M. GRAY	2/12/03		dwg no	
F	DG09-0068	Cenh	06/06/09	chr	M. GRAY	2/12/03	scale		sheet
				appd	M. GRAY	2/12/03	1:1	A	10022898
sheet index	revision sheet	F	1						

cage code
22526