Single and Dual Row Solder Pin Tails
Collet Socket – Series 518

FEATURES

- Collet Sockets available in Single or Dual Rows
- Cuttable to the number of pins desired to fit the application
- Side-to-side and end-to-end stackable



GENERAL SPECIFICATIONS

- **BODY MATERIAL**: Black UL 94V-0 Glass-filled 4/6 Nylon
- **PIN BODY**: Brass 360 1/2-hard per UNS C36000 ASTM B16/B16M-05
- **PIN BODY PLATING**: 10µ [0.25µ] min. Au per MIL-G-45204 **–OR–** 200µ [5.08µ] min. 93/7 Sn/Pb per ASTM B545 or 200µ [5.08µ] min. Sn per ASTM B545 Type 1 over 100µ [2.54µ] min. Ni per SAE AMS-QQ-N-290B
- **4-FINGER COLLET CONTACT**: BeCu per UNS C17200 ASTM B194-08
- **CONTACT PLATING**: 200µ [5.08µ] min. 93/7 Sn/Pb per ASTM B545 **–OR–** 200µ [5.08µ] min. Sn per ASTM B545 Type 1 or 10µ [0.25µ] Au per MIL-G-45204 over 50µ [1.27µ] min. [1.27µ] Ni per SAE AMS-QQ-N-290 Heavy 30µ [0.76µ]
- **CONTACT CURRENT RATING**: 3 amps
- **INSERTION FORCE**: 180g/pin, based on 0.018 [0.46] dia. test lead
- **WITHDRAWAL FORCE**: 90g/pin, based on 0.018 [0.46] dia. test lead
- **NORMAL FORCE**: 140g/pin, based on 0.018 [0.46] dia. test lead
- **OPERATING TEMPERATURE**: -67°F to 221°F [-55°C to 105°C] for Sn plating; -67°F to 257°F [-55°C to 125°C] for Au plating
- **INSERTION FORCE**: 180g/pin, based on 0.018 [0.46] dia. test lead
- **WITHDRAWAL FORCE**: 90g/pin, based on 0.018 [0.46] dia. test lead
- **NORMAL FORCE**: 140g/pin, based on 0.018 [0.46] dia. test lead
- **ACCEPTS LEADS**: 0.015-0.025 [0.38-0.64] dia.
- **LEAD LENGTHS**: from 0.100 [2.54] min.

ORDERING INFORMATION

XX X 518-1 XX XX

Additional Options
H = Heavy Au on Collet Shell
T = Sn Collet, Sn Shell
TL = Sn/Pb Collet & Shell
E = Extra Long Tail (0.183")

Plating
0 = Au Collet, RoHS Shell
0TL = Au Collet, Sn/Pb Shell
1 = Au Collet & Shell

Solder Pin Tail

Series

No. of Rows
0 = Single
1 = Dual

No. of Pins per Socket
1 Row – 1 to 40 Pins
2 Rows – 2 to 66 Pins

MOUNTING CONSIDERATIONS

- **SUGGESTED PCB HOLE SIZE**: 0.030 ±0.002 [0.76 ±0.05] dia.





"A"= NO. OF PINS PER ROW x 0.100 [2.54]
"B"= (NO. OF PINS PER ROW -1) x 0.100 [2.54]

ALL DIMENSIONS: INCHES [MILLIMETERS]
ALL TOLERANCES: ±0.005 [0.13] UNLESS OTHERWISE SPECIFIED
FOR SOCKET STRIPS WITH WIRE WRAP PINS, SEE DATA SHEETS 12021
CONSULT FACTORY FOR OTHER SIZES AND CONFIGURATIONS

CUSTOMIZATION: ARIES SPECIALIZES IN CUSTOM DESIGN AND PRODUCTION. SPECIAL MATERIALS, PLATINGS, SIZES, AND CONFIGURATIONS CAN BE FURNISHED, DEPENDING ON QUANTITY.

ARIES RESERVES THE RIGHT TO CHANGE PRODUCT GENERAL SPECIFICATIONS WITHOUT NOTICE

PRINTOUTS OF THIS DOCUMENT MAY BE OUT-OF-DATE AND SHOULD BE CONSIDERED UNCONTROLLED

ARIES ELECTRONICS, INC.
2609 Bartram Road • Bristol, PA 19007-6810 USA
TEL 215-781-9956 • FAX 215-781-9845
WWW.ARIESELEC.COM • INFO@ARIESELEC.COM

RoHS Compliant

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Aries Electronics:

12-0518-10T 40-0518-10 30-1518-11 19-0518-11H 19-0518-10H 19-0518-10T 22-0518-11H 22-1518-11H 22-1518-10T 22-1518-10H 22-0518-10T 22-0518-10H 35-0518-11H 35-0518-10H 35-0518-10T 11-0518-10H 11-0518-10T 11-0518-11H 35-0518-11 35-0518-10 39-0518-11 39-0518-10 31-0518-10 31-0518-11 37-0518-10 27-0518-11H 37-0518-11 27-0518-10H 27-0518-10T 33-0518-11 33-0518-10 38-0518-10 38-1518-10 38-1518-11 38-0518-11 30-1518-10 30-0518-10 30-0518-11 34-0518-11 34-1518-11 34-1518-10 34-0518-10 32-1518-10 32-0518-10 32-0518-11 32-1518-11 03-0518-10H 03-0518-10T 03-0518-11H 30-0518-11H 30-1518-11H 30-1518-10H 30-1518-10T 36-1518-11 36-0518-11 36-0518-10 36-1518-10 30-0518-10H 30-0518-10T 34-1518-11H 34-0518-11H 34-0518-10T 34-0518-10H 34-1518-10T 34-1518-10H 07-0518-11H 07-0518-10T 07-0518-10H 10-0518-10H 10-0518-10T 10-1518-10H 10-1518-10T 10-0518-11H 10-1518-11H 26-0518-10T 26-0518-10H 26-1518-10H 26-1518-10T 26-0518-11H 26-1518-11H 39-0518-10T 39-0518-10H 39-0518-11H 02-0518-11H 02-1518-11H 02-1518-10H 02-1518-10T 02-0518-10H 02-0518-10T 15-0518-11H 15-0518-10T 15-0518-10H 23-0518-10T 23-0518-10H 23-0518-11H 27-0518-11 27-0518-10 23-0518-10 23-0518-11 21-0518-10