



Specifications for BNC Connectors

BNC style connectors are miniature, light-weight, weatherproof interconnecting devices characterized by their two-stud, quick disconnect bayonet lock coupling arrangement. Their design functions satisfactorily from DC to 11 GHz in static applications, or from DC to 4GHz in applications involving vibration. The connectors typically yield a low VSWR (reflected signal) to 4GHz. Primary applications include radio telecommunications, broadcast equipment, medical equipment, computer, Precision Video, High definition studio broadcast, video switching and test instrumentation where frequent coupling and de-coupling are necessary. Bomar's BNCs are available in an extensive variety of configurations and cable sizes and are impedance matched to either 50 ohm or 75 ohm.

MATERIALS			
Connector Parts		Material	Equivalent Standard
Connector Body and Parts		Brass	ISOCuZn38Pb2 Body Part
Male Contact Pin		Brass	QQ-B-626
Commercial Grade		Zinc Alloy/Brass	-----
Outer Contact		Brass	QQ-B-750
Socket Contact		Beryllium Copper	QQ-C-530 / MIL-H-7199
		Phosphor Copper	CuBe2
Crimp Ferrule		Annealed Copper	QQ-C-576
Insulators, Standard Versions		Teflon	L-P403 / BS4271
		Delrin	Grade B
Rubber Gaskets		Silicone Rubber	ASTM-E1418PSI
Plating		Nickel (Silver Optional)	MIL-G-45204

ELECTRICAL			
Requirement		Performance	
Impedance		50W	75W
Frequency Range		0-4GHz	0-1 GHz
VSWR		1.30 Max.	MIL-C-39012
RF Insertion Loss		0.2 db Min. at 3 GHz	MIL-C-39012
RF Leakage		-.55 db Min. at 3 GHz	MIL-C-39012
Test Voltage (At Sea Level)		1500V rms	MIL-STD-202
Working Voltage (At Sea Level)		500V rms	MIL-STD-202
Insulation Resistance		5000 Meg ohms Min.	MIL-STD-202
Contact Resistance		3 Milli ohms Max.	MIL-C-39012

MECHANICAL & ENVIRONMENTAL		
Requirement		Test † Specification
Durability		500 Insertions & Extractions Min.
Shock		50 G
Vibration		20 G from 80-2000 Hz
Cable Retention (Cable Types)		60 lbs. Minimum Pull Test
Coupling Nut		60 lbs. Maximum
Temperature Range		Teflon: -55 to +199 C
		Delrin: -40 to +85 C
Moisture Resistance		Continuous Test
Salt Spray		48 Hours

*Products are made to conform to the MIL standard but are for commercial applications and are not QPL.

-Page1-

-Page2-



BNC 3 Piece Crimp

BNC three piece crimp connectors feature semi-captive contacts that "click" into place assuring perfect installation. Each crimp pin has a vent hole for optional soldering.

Part Number (Male)	Gender	(I.D.) **	Fig. No.	RG/U Cable
310A205A	♂	.200 In.	Fig. 1	6, 21 AWG Center Conductor
310A205A1B	♂	.200 In.	Fig. 1	6 CATV, 18 AWG Center Conductor
310A205F	♂	.124 In.	Fig. 1	58A/U, 58C/U Stranded, 141, Thin PVC
310A205FS	♂	.124 In.	Fig. 1	58/U Solid Conductor
310A205FV	♂	.125 In.	Fig. 2	58/U Thin-Net Plenum
310A205FV2	♂	.125 In.	Fig. 2	Mini 59, RGB Cable (23 AWG)
310A205FV3	♂	.125 In.	Fig. 2	Mini 59, RGB Cable (26 AWG)
310A204G	♂	.150 In.	Fig. 1	59, 62, 210
310A205G20	♂	.150 In.	Fig. 1	RG59 20 AWG Center Cond.
310A205G23	♂	.150 In.	Fig. 1	Belden 8241
310A205MV	♂	.125 In.	Fig. 3	174, 178, 196, Mini RGB Cable 50 W
310B205MV	♂	.125 In.	Fig. 3	174, 178, 196, Mini RGB Cable 75 W
310A205N	♂	.090 In.	Fig. 3	179, 187
310A205P	♂	.125 In.	Fig. 1	223
310B205Q	♂	.205 In.	Fig. 1	Belden 8281 True 75 Ohms
310A204T	♂	.150 In.	Fig. 2	59, 62, Plenum
310A208W2	♂	.103 In.	Fig. 1	Mini 59, RGB Cable (26 AWG)
♂ RoHS compliant	** crimp shank		REQUEST QUOTE	REQUEST ORDERING




Fig.1

Fig.2



Fig.3

[Click Here for Connector Dimensions/Stripping Dimensions](#)

BNC Twist-On and 2 Piece Crimp

BNC Twist-On connectors are field installable and require no tooling other than a stripping tool for the cable preparation. The center conductor is inserted into Bomar's unique Post-ConnSM contact, as the connector is twisted onto the cable's outer jacket. BNC 2 Piece crimp connectors make use of a fully captive pin. Just insert the center conductor into the connector body, slide the ferrule over the braid, and apply a single hex-crimp to the ferrule. These connectors are easy to install and reliable and are recommended only for the lower data transmission speeds.

Part Number	Gender	Fig. No.	RG/U Cable
310A405A	♂ Male	Fig. 8	6, Thick net
310A405F	♂ Male	Fig. 8	58A/U Solid Cond, 141, Thin PVC
310A405F1	♂ Male	Fig. 8	58/U Solid Cond., -172", -178"
310A405F2	♂ Male	Fig. 8	58/U Thin Plenum, -158", -162"
310A405F3	♂ Male	Fig. 8	Thin Plenum 150"
310A405G	♂ Male	Fig. 8	59, 62, 210 PVC
310A405T	♂ Male	Fig. 8	59, 62, 210 Plenum
320A405F	♀ Female	Fig. 8A	58 Solid (PVC)



Fig.8A



Fig.8

320A105G		Female	Fig. 8A	59, 62, 210 (PVC)
310X205F		Male	Fig. 6	RG58 (PVC)
310X205G		Male	Fig. 6	RG59, 62 (PVC)
320X205F		Female	Fig. 7	RG58 (PVC)
320X205G		Female	Fig. 7	RG59, 62 (PVC)
 RoHS compliant		REQUEST QUOTE REQUEST DRAWING		



Fig.6



Fig.7

FOR TECHNICAL SUPPORT: PHONE 973-347-4040 / FAX 973-347-2111 [Back to Index](#)

2

-Page 2-

- Page 3 -



BNC Connectors

BNC Standard Clamp

BNC standard clamp style is a simplified version of the original military clamp style. It is required that the contact be soldered to the center conductor of the cable.

Part Number		Gender	Fig. No.	RG/U Cable
310A105A		Male	9	6
310A105D		Male	9	11A
310A105F		Male	9	58, 58A, 58C, 141
310A105G		Male	9	59, 62, 210
310A105M		Male	9	174, 188, 316
320A105F*		Female	N/S	58, 58A, 58C, 141
320A105G*		Female	N/S	59, 62, 214



Figure 9



 RoHS compliant [REQUEST QUOTE](#) [REQUEST DRAWING](#)

BNC Specialty Broadcast Plugs

[Click here for complete Broadcast Catalog](#)

Broadcast grade BNC connectors are perfectly matched to 75 ohm impedance's. The superior plugs are for studio wiring and other broadcast uses. Solid precision machined brass, not die-cast, hold up under the toughest conditions. Here, we are showing the eight most popular but there are many more versions matched to the popular cable manufacturer's part number.



Part Number		Gender	Belden Cable
SBC1505A		Male	1505A
SBC1694A		Male	1694A
SBC1695A		Male	1695A
SBC1855A		Male	1855A
SBC7731A		Male	7731A
SBC8218		Male	8218
SBC8241		Male	8241
SBC8281		Male	8281

 RoHS compliant [REQUEST QUOTE](#) [REQUEST DRAWING](#)

BNC Bulkhead Jacks

Versions are available for front mounting, (F/M) rear mounting, (R/M) crimp types, bulkhead mount grounded, or bulkhead mount, isolated. (Color-coded available.) These jacks are held into the panel by a hex-nut and lock washer. All units feature nickel plated, brass bodies, and gold phosphor-bronze contacts



Figure 13



Figure 14



Figure 15



Figure 16

Part Number		Description	Fig No.	Hole ID	Dwg
321A245A		R/M Crimp, RG6	13	.500	
321A245F		R/M Crimp, RG58 , Thin-net PVC	13	.500	
321A245FV		R/M Crimp, Thin-Net Plenum	13	.500	
321A245G		R/M Crimp, RG59, 62, 210	13	.500	
321A245M		R/M Crimp, RG174, 188, 196, 316	13	.500	
321B245M*		R/M Crimp, RG174, 188, 196, 316	13	.500	
321B245N*		R/M Crimp, RG179, 187	N/S	.500	
326A515		F/M Solder (Grounded)	14	.375	
326R515		F/M Solder (Isolated) White Bushing	15	.375	
326R51SRD		F/M Solder (Isolated) Red Bushing	16	.375	
326R51SGN		F/M Solder (Isolated) Green Bushing	16	.375	
326R51SBL		F/M Solder (Isolated) Blue Bushing	16	.375	

 RoHS compliant

[REQUEST QUOTE](#) [REQUEST](#)

[DRAWING](#)

FOR TECHNICAL SUPPORT: PHONE 973-347-4040 / FAX 973-347-2111 [Back to Index](#)

3


- Page 4 -



BNC Panel Jacks and Plugs

BNC panel plugs and jacks are of machined brass construction for maximum reliability and quality. All contacts are plated with a minimum of five micro-inches of gold. The square panel types mount on .500 inch centers. The bulkhead type mounts into a .380 "D" shaped panel hole. All connector bodies are bright-nickel plated.

Part Number		Description	Notations	Fig. No.	Dwg.
316A524C		Male Bulkhead Panel Mount	.300" Mfg. Hole	19	
317A507		Male Panel Mount	.500 Mfg. Hole Centers	20	
321A205F		Female Panel Mount, Crimp	Fin RG58/U Cables	21	
321A205G		Female Panel Mount, Crimp	Fin RG59, 62, 210	21	
321A205M		Female Panel Mount, Crimp	Fin RG174, 178, 196	21	
327A507		Female Panel Mount, Solder	.500 Mfg. Hole Centers	22	
RoHS compliant REQUEST QUOTE REQUEST DRAWING					



BNC PC Board Vertical Jacks

BNC vertical mount jacks are available in straight PC mounts and "through-panel" styles. The "through-panel", 364 Series, is made in both isolated and grounded versions and are ideal for applications where multiple insertions will require a connector which can endure the stress of higher torque.

Part Number		Body Plating or Material	Description	Insul. Mat.	Con. Plating	"L," Dim	Fig. No.	Dwg.
361A514*		Nickel / Brass	Straight PC Mount 50W	Teflon	Gold	.717	26	
361A505*		Nickel / Brass	Straight PC Mount 50 W	Delrin	Gold	.914	27	
361A534*		Nickel / Brass	3 Post PC Mount 50 W	Delrin	Gold	.788	27A	
361A505APF		Nickel/Zinc	4 Post W/ Press Fit Center Pin 50W	Delrin	Gold	.925	27B	
361A705APF		Nickel/Zinc	4 Post W/ Press Fit Center Pin 75W	Delrin	Gold	.925	27B	
364S595		White Valox	PC Mount, Thru-Panel, 50 W	Delrin	Gold	1.36	23	
364S595B		Black Valox	PC Mount, Thru-Panel, 50 W	Delrin	Gold	1.36	24	
364S595M		Nickel/Zinc	PC Mount, Thru-Panel, 50 W	Delrin	Gold	1.36	25	
364S795*		White Valox	PC Mount, Thru-Panel, 75 W	Delrin	Gold	1.36	23	
364S795B*		Black Valox	PC Mount, Thru-Panel, 75 W	Delrin	Gold	1.36	24	
364S795M*		Nickel/Zinc	PC Mount, Thru-Panel, 75 W	Delrin	Gold	1.3	25	
RoHS compliant reflow or wave solder RoHS compliant wave solder only REQUEST QUOTE REQUEST DRAWING								





Fig. 26




Fig. 27B




Fig. 27A

* Denotes that items are not popular and may require a special minimum quantity requirement.

FOR TECHNICAL SUPPORT: PHONE 973-347-4040 / FAX 973-347-2111 [Back to Index](#)

4

- Page 4 -

- Page 5 -



BNC Connectors

BNC PC Board Right Angle Jacks

These BNC jacks are manufactured to the highest standards to assure stability in maintaining impedance matching at 50 ohm and 75 ohm applications. The 50 ohm versions have been approved by most of the U.S. manufacturers of LAN cards, and the 75 ohm is in wide use in High Definition Video applications which require the use of a True 75 ohm connector. Contacts are phosphor bronze and will remain resilient even after hundreds of insertions.




Fig. 28 lg.

Fig. 29






Fig. 30

Fig. 31



Part Number		Body Material	Description	Imp.	Height F.M.S.	Contact Plating	Fig. No.	Dwg.
364M095		Nickel/Zinc	4 Post Low Profile, Metal	50W	.453	Gold	38	
364M0975		Nickel / Zinc	4 Post Low Profile, Metal	75W	.453	Gold	38	
364A595		White Valox	Standard Profile W/ Posts	50W	.610	Gold	28	
364A595T		White Valox	Standard Profile W/ Posts (TPX)	50W	.610	Gold	28	
364A595NP*		White Valox	Standard Profile WO Posts	50W	.610	Gold	35	
364A595NP1*		White Valox	Standard Profile WO Posts (TPX)	50W	.610	Gold	35	
364A595B		Black Valox	Standard Profile W/ Posts	50W	.610	Gold	30	
364A595BT		Black Valox	Standard Profile W/ Posts (TPX)	50W	.610	Gold	30	
364A595BNP*		Black Valox	Standard Profile WO Posts	50W	.610	Gold	35	
364A595BNP1*		Black Valox	Standard Profile WO Posts (TPX)	50W	.610	Gold	35	
364A595BL		White Valox	Lo Profile W/ Posts	50W	.515	Gold	29	
364A595BLT		White Valox	Lo Profile W/ Posts (TPX)	50W	.515	Gold	29	
364A595BLNP*		White Valox	Lo-Profile W/O Posts	50W	.515	Gold	34	
364A595BLB		Black Valox	Lo-Profile W/ Posts	50W	.515	Gold	31	
364A595BLBT		Black Valox	Lo-Profile W/ Posts (TPX)	50W	.515	Gold	31	
364A595BLBNP*		Black Valox	Lo-Profile W/O Posts	50W	.515	Gold	34	




364M595		Nickel / Zinc	Standard Profile W/ Posts	50W	.620	Gold	32	
364M595T		Nickel / Zinc	Standard Profile W/ Posts (TPX)	50W	.620	Gold	32	
364M595M		Nickel / Zinc	Super Lo-Profile W/ Clips	50W	.340	Gold	35A	
364M595MT		Nickel / Zinc	Super Lo-Profile W/ Clips (TPX)	50W	.340	Gold	35A	
364M595L		Nickel / Zinc	Lo-Profile W/ Posts	50W	.529	Gold	33	
364M595LT		Nickel / Zinc	Lo-Profile W/ Posts (TPX)	50W	.529	Gold	33	
364A795		White Valox	Standard Profile W/ Posts (TPX)	75W	.610	Gold	28	
364A795T		White Valox	Standard Profile W/ Posts	75W	.610	Gold	28	
364A795B		Black Valox	Standard Profile W/ Posts	75W	.610	Gold	30	
364A795BT		Black Valox	Standard Profile W/ Posts (TPX)	75W	.610	Gold	30	
364A795BL		White Valox	Lo-Profile W/ Posts	75W	.515	Gold	29	
364A795BLT		White Valox	Lo-Profile W/ Posts (TPX)	75W	.515	Gold	29	
364A795BLB		Black Valox	Lo-Profile W/ Posts	75W	.515	Gold	31	
364A795BLBT		Black Valox	Lo-Profile W/ Posts (TPX)	75W	.515	Gold	31	
364M795		Metal	Standard Profile W/ Posts	75W	.620	Gold	32	
364M795T		Metal	Standard Profile W/ Posts (TPX)	75W	.620	Gold	32	
364M795L		Metal	Lo-Profile W/ Posts	75W	.529	Gold	33	
364M795LT		Metal	Lo-Profile W/ Posts (TPX)	75W	.529	Gold	33	
364F595BL		White Valox	9400pF 500V Decoupled	50W	.515	Gold	36	---
364F595BLB		Black Valox	9400 pF 500V Decoupled	50W	.515	Gold	37	---
364F595BL		White Valox	9400 pF 1500V Decoupled	50W	.515	Gold	36	---
364F595BLB		Black Valox	9400 pF 1500V Decoupled	50W	.515	Gold	37	---
364NT		Zinc/Brass	Jam Nut (364 Series)	N/A	----	----	38N	
364LW		Zinc/ Steel	Lock Washer (364Series)	N/A	----	----	37N	
364 KNT		Brass/Nickel	Knurled Nut (364 Series)	N/A	----	----	38N	

Board Clips Are Available In Place of Posts. Add Suffix "C"



Spear-point clips lock snugly into the board.

Hardware



FOR TECHNICAL SUPPORT: PHONE 973-347-4040 / FAX 973-347-2111 [Back to Index](#)

5

- Page 5 -

- Page 6 -



BNC V-Bite ® PC Edge Mount

The V-Bite ® is an industry award winning design PCB connector with all the advantages a designer could want. It edge mounts to the board which offers the lowest profile and utilizes very little PCB real estate. It lends itself to surface mount and through-hole soldering techniques. There are versions for IR and convection reflow soldering. Because the connector locks into place both above and below the PCB it dispenses rotational torque relief to the board and not the solder points. The V-Bite ® design offers the lowest VSWR ratings due to the straight through-put contact design. No right angles for reflection. Available in 50 and 75 ohm, threaded and non-threaded. Other options for PCB thickness available. Other interfaces available.

(See "F", BNC Twin and TNC sections.)

Part Number		Description	Imp	Contact	Fig. No.	Prog.
361V504ER		BNC Jack W/ Teflon For Reflow Solder	50W	Brass./Gold	39A	
361V504ET		BNC Threaded Jack W/ Teflon For Reflow Solder	50W	Brass./Gold	39	
361V504EFT		BNC Threaded Jack W/ Teflon Insulator/Flange	50W	Brass./Gold	39B	
361V509E		BNC Jack W/ Polyethylene Insulator	50W	Brass./Tin	39A	---
361V509ET		BNC Threaded Jack W/ Polyethylene Insulator	50W	Brass./Tin	39	---
361V704ER		BNC Jack W/ Teflon For Reflow Solder	75W	Brass./Gold	39A	
361V704ET		BNC Threaded Jack W/ Teflon For Reflow Solder	75W	Brass./Gold	39	
361V704EFT		BNC Threaded Jack W/ Teflon Insulator/Flange	75W	Brass./Gold	39B	
361V709E		BNC Jack W/ Polyethylene Insulator	75W	Brass./Gold	39A	---
361V709ET		BNC Threaded Jack W/ Polyethylene Insulator	75W	Brass./Gold	39	---



Fig. 39


The Super Low™ Profile BNC PC jack reduces the amount of board space needed to mount a PC jack. Board clips hold the unit in place for soldering. The smallest, lowest profile right angle BNC jack available.

The Lo-Deco™ features a four post design that offers greater stability after wave soldering. Also featured is a gold plated contact and nickel plated cast zinc body. Smooth, sleek and aesthetically pleasing design is tumbled to remove casting lines.

Fig 35A



Fig. 38



PC Layout for Super Low Profile

*Denotes that items are not popular and may require a special minimum order quantity.



BNC Connectors

Right Angle or Vertical Stacked: When board space becomes a serious issue and you still need the robust, full size, BNC connectors, a dual stacked right angle or vertical version will do the trick. Assembly insertion time is cut in half as well. The Dual 364 series is available in both Valox isolated and all metal construction.

(shown with closed back option FS)



Fig. 38



Fig. 38



Fig. 40D



Fig. 38C




Fig. 38L



Fig. 38E

		Right Angle				
Part Number		Description	Imp.	Contact	Fig.No.	Dwg.
364A2595	✓	Dual Right Angle, White Valox	50W	Phos./Gold	38A	
364A2595T		Dual Right Angle, White Valox (TPX)	50W	Phos./Gold	38A	
364A2795	✓	Dual Right Angle, White Valox	75W	Phos./Gold	38A	
364A2795T		Dual Right Angle, White Valox (TPX)	75W	Phos./Gold	38A	
364A2595B	✓	Dual Right Angle, Black Valox	50W	Phos./Gold	38A	
364A2795B	✓	Dual Right Angle, Black Valox	75W	Phos./Gold	38A	
364M2595	✓	Dual Right Angle, Metal	50W	Phos./Gold	38B	
364M2595T		Dual Right Angle, Metal (TPX)	50W	Phos./Gold	38B	
364M2795	✓	Dual Right Angle, Metal	75W	Phos./Gold	38B	
364M2795T		Dual Right Angle, Metal (TPX)	75W	Phos./Gold	38B	
3M64M2795	✓	Dual Right Angle, Metal Mini-BNC	75W	Phos./Gold	38C	
364KNUT		Knurled Nut for Dual BNC	N/A	Brass/Nickel	38D	
Vertical						
Part Number		Description	Imp.	Contact	Fig.No.	Dwg.
364S2595	✓	Dual Vertical, White Valox	50W	Phos./Gold	40D	
364S2795	✓	Dual Vertical, White Valox	75W	Phos./Gold	40D	
364S2595B	✓	Dual Vertical, Black Valox	50W	Phos./Gold	40D	
364S2795B	✓	Dual Vertical, Black Valox	75W	Phos./Gold	40D	
364S2595M	✓	Dual Vertical, Metal	50W	Phos./Gold	----	
364S2795M	✓	Dual Vertical, Metal	75W	Phos./Gold	----	
Tool						
Part Number		Description	Imp.	Contact	Fig.No.	Dwg.
BD36400	-	Hex Shafted Tool for Knurled Nut	N/A	Steel/Nickel	38E	

 RoHS Compliance or aware solder
  RoHS Compliance
  RoHS Compliance was solder only

[REQUEST QUOTE](#)
[REQUEST DRAWING](#)

Note: Hardware is optional and must be ordered separately

BNC Multi-Port PC Jacks (Non-Threaded)

Side By Side: These right angle units are available in dual or quad configurations. These units are not threaded for panel installation using a jam nut. Up one fourth the installation time.

Part Number		Description	Imp.	Contact	Fig. No.
365A2595	✓	Dual Right Angle, Side By Side White Valox	50W	Phos./Gold	38B
365A2795	✓	Dual Right Angle, Side By Side White Valox	75W	Phos./Gold	38B
365A2595B	✓	Dual Right Angle, Side By Side Black Valox	50W	Phos./Gold	38B
365A2795B	✓	Dual Right Angle, Side By Side Black Valox	75W	Phos./Gold	38B
365A4595	✓	Quad Right Angle, Side By Side White Valox	50W	Phos./Gold	NS
365A4795	✓	Quad Right Angle, Side By Side White Valox	75W	Phos./Gold	NS
365A4595B	✓	Quad Right Angle, Side By Side Black Valox	50W	Phos./Gold	NS
365A4795B	✓	Quad Right Angle, Side By Side Black Valox	75W	Phos./Gold	NS

RoHS compliant  refine or wave solder ✓ RoHS compliant wave solder only [REQUEST QUOTE](#) [REQUEST DRAWING](#)



Fig.38B

FOR TECHNICAL SUPPORT: PHONE 973-347-4040 / FAX 973-347-2111 [Back to Index](#)



BNC Adapters

These sturdy within-series BNC adapters are available in all standard designs. Additionally, several unique constructions compliment the product group and allow adaptations for every conceivable application. All connector bodies are plated with bright nickel. Male contacts are brass, female contacts are phosphor bronze. All contacts are plated with 5 micro inches of gold.

Part Number		Description	Fig. No.
330A505		Male/ Male Inline Barrel Splice	35
332A505		Female/Female Inline Splice	36
335A544		Female/Female Inline Bulkhead Mount (Grounded)	37
335K544		Female/Female Inline Isolated Bulkhead (Metal Outer Thread)	37
343A205F		Crimp "T" Adapter for RG58 Cable	41
343A205G		Crimp "T" Adapter for RG59, 62 Cables	41
343A505		Female/Male/Female "T" Adapter (Yes, it runs with Netware™)	38
345A505		Female/Female/Female "T" Adapter	39
351A505		Female/Male Right Angle Adapter	40
383U505		The Goalie™	42
383U205F		The Goalie Brute™ Crimp Version for RG58 Cable	45
383U205G		The Goalie Brute™ Crimp Version for RG59, 62 Cables	45
383K505*		The Goalie Brute™	43
383P505*		The Insulated Goalie	44
353U205F*		Male/Female/Female Right Angle Double-Down™Crimp for RG58	49
353U205G*		Male/Female/Female Right Angle Double-Down™ Type for RG59	49
353U505*		Male/Female/Female Right Angle Double-Down™	48
393U205F*		Male/Female/Female Straight Double-Down™Crimp for RG58	47
393U205G*		Male/Female/Female Straight Double-Down™Crimp for RG59	47
393U505*		Male/Female/Female Straight Double-Down™	46

 RoHS compliant [REQUEST QUOTE](#) [REQUEST DRAWING](#)




Fig. 39




Fig. 38




Fig. 40

Fig. 42




Fig. 43

Fig. 46




Fig. 45




Fig. 35

Fig. 36

Fig. 37




Fig. 41

Fig. 49

Specialty LAN Adapters

Double Down™ adapters are designed to allow parallel cables entering a patch panel, or a BNC LAN terminal port to be guided at a right angle to the input jack. Two versions accomplish this: one is a right angle with side-by-side jacks for areas with little rear clearance, and the other is a straight version for installations where width between panel jacks is limited. Crimp types are for permanent installations. Goalie, and Goalie Brute allow parallel cable 90° entry which require a minimum of rotational cable space.



*Minimum quantity Requirements May Apply - Contact Sales

FOR TECHNICAL SUPPORT: PHONE 973-347-4040 / FAX 973-347-2111 [Back to Index](#)

9

- Page 9 -

- Page 10 -



BNC Connectors

BNC Terminators

BNC terminators are available in standard 1% tolerance versions and in the economy 5% tolerance styles. The standard types have removable color coded caps for easy identification. The economy type are color coded as well but caps are not removable.

Part Number		Description	Fig. No.
310X054A		50 W with Red Cap	50
310C054		50 W with Grounding Chain	51
310X074		75 W with Blue Cap	50
HBC310X075		75 W Precision .1% Tolerance	52
310X094		93 W with Yellow Cap	50
HBC310X075		75 W Precision .1% Tolerance	53
EJ175		50 W Economy	N/S
EJ177		75 W Economy	N/S
EJ179		93 W Economy	N/S
RoHS compliant REQUEST QUOTE REQUEST DRAWING			



Fig. 50



Fig. 51



Fig. 52

FOR TECHNICAL SUPPORT: PHONE 973-347-4040 / FAX 973-347-2111 [Back to Index](#)

10

- Page 10 -



Coax Crimp Tools

Professional grade hex-crimp tools for coaxial connectors are available in ratchet and non-ratcheting types, both provide dependable service. Ratchet tools feature replaceable dies. Included is a convenient release mechanism to unlatch the ratchet in the event of an improper crimp. Each too also crimps the contact pin to the conductor.

Part Number	Description
BD10100	Hex Crimp Ratchet for "F" Types, RG59, RG6
BDHD100	Hex Crimp Ratchet for Belden 8281
BDHD200	Hex Crimp Ratchet for BNC/TNC RG58,59,62 and MV
BDHD100	Hex Crimp Ratchet for Mini-RG59
BD11012	Hex Crimp Ratchet for "N" Crimp RG11, RG213, RG214
BDHD100	Hex Crimp Ratchet for BNC/TNC, RG6, RG59

[REQUEST QUOTE](#)

- Page 11 -