



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	2 AWG
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric
Wire Strip Length	15/16 in.
Stud Size	1/4 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	BROWN
Panduit Die Index No. on Barrel	P33
Alternate Industry Die Index No. ( ) on Barrel	(10)



LISTED  
Wire Connector



02	1/11	JHNU	JHNU	REVISED OVERALL HEIGHT: WAS 1.38 REVISED TONGUE THICKNESS: WAS .11	
REV	DATE	BY	CHK	DESCRIPTION	ECN

**PANDUIT**

**CORP. TINLEY PARK, ILLINOIS**

LCDN2-14AF-Q  
Copper Lug - Two-Hole Narrow Tongue, Standard Barrel, 90° Angle Tongue

SCALE  
N/A

DRAWING NO / CAD FILE

LCDN2-14AF-CUST