





SWITCH-ENCLOSED

CATALOG LISTING
4CE7



CIRCUIT DIAGRAM



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE - - - - - 6-12 LB	CONTACT ARRANGEMENT SEE CIRCUIT DIAGRAM	DO NOT SCALE PRINT
FULL OVERTRAVEL FORCE - - - 30 LB MAX		UNLESS OTHERWISE NOTED
RELEASE FORCE - - - - - 5 LB MIN		DIMENSIONS ARE IN INCHES
PRETRAVEL - - - - - .070 MAX		TOLERANCES ARE:
DIFFERENTIAL TRAVEL - - - .045 MAX	10 A-125 OR 250 VAC	ONE PLACE (.0) ±.030
OVERTRAVEL - - - - - .230 MIN		TWO PLACE (.00) ±.015
		THREE PLACE (.000) ±.005
		ANGLES ±.005
		WEIGHT 12.5 OZ MAX

NOTE -

- 1- ALUMINUM ALLOY ENCLOSURE ANODIZED, IMPREGNATED AND FINISHED WITH ONE COAT OF PRIMER
- 2- CIRCUIT IDENTIFICATION SHOWN ON NAMEPLATE
- 3- SHOCKPROOF PER MIL-S-901 GRADE I, TYPE C, LIGHT-WEIGHT
- 4- EQUIPMENT WITH NO PHYSICAL DAMAGE
- 5- WATERTIGHT PER MIL-STD-108, TABLE III, METHOD C, AT 1.3 PSI
- FOR 2 HOURS WHEN USED WITH MATING RECEPTACLE MS3106E-18-1S OR EQUIVALENT
- 6- FURNISHED WITH SNUG FITTING PLASTIC DUST CAP

4CE7

M

DRAWING
NUMBER

8

8

ISSUE

8

REVISIONS

A	SR11445	L S D	3 FEB 64
B	SR11445	OM W	18 FEB 64
C	CO19325	H B W	18 JUN 64
D	CO21356	L S D	7 APR 66
E	CO-53016	K A G	23 JUN 83
		D	CO 58411
		C J H	15 NOV 85
		E	204537
		S A V	14 DEC 01

REPLACES

RELEASE NO. SR11445

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[4CE7](#)