

THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
© 2003, Projects Unlimited Inc.




SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED VOLTAGE (SQUARE WAVE)	12	Vp-p
OPERATING VOLTAGE RANGE	6 ~ 15	Vp-p
RATED CURRENT (MAX)	40	mA
COIL RESISTANCE	120±18	OHM
MINIMUM SPL @ 10 CM	80	dBA
RESONANT FREQUENCY	2,250±250	Hz
OPERATING TEMPERATURE	-20 ~ +80	°C
STORAGE TEMPERATURE	-30 ~ +85	°C
HOUSING MATERIAL	NORYL	-
TERMINAL MATERIAL	TIN-PLATED COPPER	-
WEIGHT	7	grams

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
-	RELEASED FROM ENGINEERING	5/1/02	
A	REVISED TEMPERATURE RANGE ETC.	12/31/02	S. J.
B	REVISED TO NEW TEMPLATE	6/15/04	R. W.
C	REVISED SPL & FREQUENCY VALUES	10/05/05	B. R.

SOUND EMISSION
HOLE



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN
MILLIMETERS, TOLERANCES ARE ±0.5 AND
ANGLES ARE ±3°.

APPROVALS	DATE
DRAWN <i>RABL</i>	5/02
APPROVED <i>S. J.</i>	5/02
DO NOT SCALE DRAWING	



Dayton , Ohio

TRANSDUCER(ELECTRO-MECH)
AT-203

SIZE
A

DRAWING NO.
AT-203

SCALE: N.T.S.

SHEET 1 OF 1

FILE NAME
AT-203.DWG