

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0009752064](#)
Status: **Contact Molex**
Overview:
Description: 3.96mm (.156") Pitch SPOX™ and KK® Wire-to-Board and Board-to-Board Header, Right Angle, with Friction Lock, 6 Circuits

Documents:


- [3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-5195-001 \(PDF\)](#)
[Product Specification PS-5195-005 \(PDF\)](#)
[Product Specification PS-5239-002 \(PDF\)](#)
- [Product Specification PS-5239-004 \(PDF\)](#)
[Product Specification PS-5239-006 \(PDF\)](#)
[Product Specification PS-5239-007 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	PCB Headers
Series	5274
Application	Wire-to-Board
Overview	KK®
Product Name	KK®
Product Name	SPOX™

Physical

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-2
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Number of Rows	1
Orientation	Right Angle
PC Tail Length (in)	0.142 In
PC Tail Length (mm)	3.60 mm
PCB Locator	No
PCB Retention	None
PCB Thickness Recommended (in)	0.062 In
PCB Thickness Recommended (mm)	1.60 mm
Packaging Type	Bag
Pitch - Mating Interface (in)	0.156 In
Pitch - Mating Interface (mm)	3.96 mm
Plating min: Mating (µin)	200
Plating min: Mating (µm)	5
Plating min: Termination (µin)	200
Plating min: Termination (µm)	5
Polarized to PCB	No
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C



Series image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Not Reviewed
**Halogen-Free
Status**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
[5274](#) Series

Mates With
[5195](#) SPOX™ Crimp Housing. [5239](#) KK®
Crimp Housing

Termination Interface: Style	Through Hole
Electrical	
CSA	LR19980
Current - Maximum	7A
UL	E29179
Voltage - Maximum	250V
Material Info	
Old Part Number	5274-06A
Reference - Drawing Numbers	
Product Specification	PS-5195-001
Product Specification	PS-5195-005
Product Specification	PS-5239-002
Product Specification	PS-5239-004
Product Specification	PS-5239-006
Product Specification	PS-5239-007
Sales Drawing	SD-5274-NA

This document was generated on 11/05/2009

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION