


FES16AT THRU FES16JT

FAST EFFICIENT PLASTIC RECTIFIER

Reverse Voltage - 50 to 600 Volts

Forward Current - 16.0 Amperes

TO-220AC



Dimensions in inches and (millimeters)

FEATURES

- ♦ Plastic package has Underwriters Laboratory Flammability Classification 94V-0
- ♦ Glass passivated chip junction
- ♦ Low power loss
- ♦ Low forward voltage, high current capability
- ♦ High surge current capability
- ♦ Superfast recovery time, for high efficiency
- ♦ High temperature soldering guaranteed: 250°C, 0.16" (4.06mm) from case for 10 seconds



MECHANICAL DATA

Case: JEDEC TO-220AC molded plastic body over passivated chips

Terminals: Plated lead solderable per MIL-STD-750, Method 2026

Polarity: As marked

Mounting Position: Any

Weight: 0.064 ounce, 1.81 grams

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

	SYMBOLS	FES 16AT	FES 16BT	FES 16CT	FES 16DT	FES 16FT	FES 16GT	FES 16HT	FES 16JT	UNITS
Maximum repetitive peak reverse voltage	V _{RRM}	50	100	150	200	300	400	500	600	Volts
Maximum RMS voltage	V _{RMS}	35	70	105	140	210	280	350	420	Volts
Maximum DC blocking voltage	V _{DC}	50	100	150	200	300	400	500	600	Volts
Maximum average forward rectified current at T _C =100°C	I _(AV)	16.0								Amps
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method) at T _C =100°C	I _{FSM}	250.0								Amps
Maximum instantaneous forward voltage at 16A	V _F	0.975				1.3		1.5		Volts
Maximum DC reverse current T _C =25°C at rated DC blocking voltage T _C =100°C	I _R	10.0 500.0								μA
Maximum reverse recovery time (NOTE1)	t _{rr}	35.0				50.0				ns
Typical junction capacitance (NOTE 2)	C _J	175.0						145.0		pF
Typical thermal resistance (NOTE 3)	R _{θJA} R _{θJC}	16.0 1.2								°C/W
Operating and storage temperature range	T _J , T _{STG}	-65 to +150								°C

NOTES:

- (1) Reverse recovery test conditions: I_F=0.5A, I_R=1.0A, I_{rr}=0.25A
- (2) Measured at 1.0 MHz and applied reverse voltage of 4.0 Volts
- (3) Thermal resistance from junction to case and ambient mounted on heatsink

RATINGS AND CHARACTERISTICS CURVES FES16AT THRU FES16JT

FIG. 1 - FORWARD CURRENT DERATING CURVE




FIG. 2 - MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




FIG. 4 - TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG. 3 - TYPICAL REVERSE CHARACTERISTICS




FIG. 5 - TYPICAL JUNCTION CAPACITANCE

