




PART NO.
SEE CHART
DWG. NO.
SDA-90628



CKT SIZE	DIM. "A"		DIM. "B" (± 0.20 $\pm .008$)		CKT SIZE	DIM. "A"		DIM. "B" (± 0.20 $\pm .008$)	
2X 1			(2.54)	.100	2X21	(50.80)	2.000	(53.34)	2.100
2X 2	(2.54)	.100	(5.08)	.200	2X22	(53.34)	2.100	(55.88)	2.200
2X 3	(5.08)	.200	(7.62)	.300	2X23	(55.88)	2.200	(58.42)	2.300
2X 4	(7.62)	.300	(10.16)	.400	2X24	(58.42)	2.300	(60.96)	2.400
2X 5	(10.16)	.400	(12.70)	.500	2X25	(60.96)	2.400	(63.50)	2.500
2X 6	(12.70)	.500	(15.24)	.600	2X26	(63.50)	2.500	(66.04)	2.600
2X 7	(15.24)	.600	(17.78)	.700	2X27	(66.04)	2.600	(68.58)	2.700
2X 8	(17.78)	.700	(20.32)	.800	2X28	(68.58)	2.700	(71.12)	2.800
2X 9	(20.32)	.800	(22.86)	.900	2X29	(71.12)	2.800	(73.66)	2.900
2X10	(22.86)	.900	(25.40)	1.000	2X30	(73.66)	2.900	(76.20)	3.000
2X11	(25.40)	1.000	(27.94)	1.100	2X31	(76.20)	3.000	(78.74)	3.100
2X12	(27.94)	1.100	(30.48)	1.200	2X32	(78.74)	3.100	(81.28)	3.200
2X13	(30.48)	1.200	(33.02)	1.300	2X33	(81.28)	3.200	(83.82)	3.300
2X14	(33.02)	1.300	(35.56)	1.400	2X34	(83.82)	3.300	(86.36)	3.400
2X15	(35.56)	1.400	(38.10)	1.500	2X35	(86.36)	3.400	(88.90)	3.500
2X16	(38.10)	1.500	(40.64)	1.600	2X36	(88.90)	3.500	(91.44)	3.600
2X17	(40.64)	1.600	(43.18)	1.700	2X37	(91.44)	3.600	(93.98)	3.700
2X18	(43.18)	1.700	(45.72)	1.800	2X38	(93.98)	3.700	(96.52)	3.800
2X19	(45.72)	1.800	(48.26)	1.900	2X39	(96.52)	3.800	(99.06)	3.900
2X20	(48.26)	1.900	(50.80)	2.000	2X40	(99.06)	3.900	(101.60)	4.000




- NOTES
- FOR ASSY NUMBERS WITH FINISH OPTIONS
AND DIMS C & D SEE SUBSEQUENT SHEETS.
 - PCB THICKNESS: $(1.37-1.80) / .054-.071$.



RECOMMENDED P.C. BOARD HOLE PATTERN

OPPOSING KINKS
VIEW SHOWS 2 X 1 CCT ONLY



STRAIGHT PINS
OMMITTED FROM VIEW

FOR PREVIOUS
DRAWING ISSUES
SEE MRI.

NEW RELEASE ECR E00166 11 SEPTEMBER 1990 RD	REVISIONS	DIMENSIONS SHOWN (METRIC) INCH UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR $\pm \frac{1}{2}^\circ$ INCH (METRIC)		DRWG BY RD	REVISE ONLY ON CAD SYSTEM	
		3 PLACE $\pm .$			CAD/CAM FILE NAME SA90628X1 DCN	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. & SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION
B	LTR	2 PLACE $\pm .004$	$\pm .10$	CHK'D BY	TITLE	
		1 PLACE $\pm .$	$\pm .25$		C-GRID III DUAL ROW KINKED PIN HEADER	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		APP'D BY	SHEET NO. DATE	
		DESIGN DIMENSION (PRIMARY)	☒ (MM) ☐ IN.		10F2	90/09/11
		EQUIVALENT DIMENSION (SECONDARY)	☐ (MM) ☒ IN.	SCALE 4:1	PART NO. SEE CHART	
					DWG NO. SDA-90628	SIZE B

	10	9	8	7	6	5	4	3	2	1	
F	PART NO. SEE CHART SDA-90628	CIRCUIT SIZE	PLATING TYPE A PART NO.	PLATING TYPE E PART NO.	PLATING TYPE F PART NO.	KINKED PIN POSITIONS					F
E			2 X 1	90628 -0121	90628 -0761	90628 -0921	1				
D	DIM C (±0.25) ±.010 (6.75) .266	2 X 2	↑ -0122	↑ -0762	↑ -0922	1,3					D
		2 X 3	-0123	-0763	-0923	1 & 5					
C	DIM D (±0.30) ±.012 (2.90) .114	2 X 4	-0124	-0764	-0924	3 & 5					C
		2 X 5	-0125	-0765	-0925	3 & 7					
B		2 X 6	-0126	-0766	-0926	5 & 7					B
		2 X 7	-0127	-0767	-0927	5 & 9					
A		2 X 8	-0128	-0768	-0928	7 & 9					A
		2 X 9	-0129	-0769	-0929	7 & 11					
		2 X 10	-0130	-0770	-0930	9 & 11					
		2 X 11	-0131	-0771	-0931	1,11 & 21					
		2 X 12	-0132	-0772	-0932	1,12 & 23					
		2 X 13	-0133	-0773	-0933	1,13 & 25					
		2 X 14	-0134	-0774	-0934	1,15 & 27					
		2 X 15	-0135	-0775	-0935	1,15 & 29					
		2 X 16	-0136	-0776	-0936	1,15 & 31					
		2 X 17	-0137	-0777	-0937	1,17 & 33					
		2 X 18	-0138	-0778	-0938	1,17 & 35					
		2 X 19	-0139	-0779	-0939	1,19 & 37					
		2 X 20	-0140	-0780	-0940	1,19 & 39					
		2 X 21	-0141	-0781	-0941	1,21 & 41					
		2 X 22	-0142	-0782	-0942	1,21 & 43					
		2 X 23	-0143	-0783	-0943	1,23 & 45					
		2 X 24	-0144	-0784	-0944	1,23 & 47					
		2 X 25	-0145	-0785	-0945	1,25 & 49					
		2 X 26	-0146	-0786	-0946	1,25 & 51					
		2 X 27	-0147	-0787	-0947	1,27 & 53					
		2 X 28	-0148	-0788	-0948	1,27 & 55					
		2 X 29	-0149	-0789	-0949	1,29 & 57					
		2 X 30	-0150	-0790	-0950	1,29 & 59					
		2 X 31	-0151	-0791	-0951	1,31 & 61					
		2 X 32	-0152	-0792	-0952	1,31 & 63					
		2 X 33	-0153	-0793	-0953	1,33 & 65					
		2 X 34	-0154	-0794	-0954	1,33 & 67					
		2 X 35	-0155	-0795	-0955	1,35 & 69					
		2 X 36	-0156	-0796	-0956	1,35 & 71					
		2 X 37	-0157	-0797	-0957	1,37 & 73					
		2 X 38	-0158	-0798	-0958	1,37 & 75					
		2 X 39	↓ -0159	↓ -0799	↓ -0959	1,39 & 77					
		2 X 40	90628 -0160	90628 -0800	90628 -0960	1,39 & 79					
NOTES: 1. FOR PLATING VARIATIONS SEE ENG.STD. SDES-99000-0003.											
FOR PREVIOUS DRAWING ISSUES SEE MRI. SEE SHEET 1. REVISIONS LTR DIMENSIONS SHOWN (METRIC) INCH UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1/2° 3 PLACE ± . 2 PLACE ± . 1 PLACE ± . DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS DESIGN DIMENSION (PRIMARY) (MM) [X] IN. [] EQUIVALENT DIMENSION (SECONDARY) (MM) [] IN. [X] DRWG BY RD CHK'D BY APP'D BY SCALE REVISE ONLY ON CAD SYSTEM SHL REV. CAD/CAM FILENAME SA90628X2 DGN THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. & SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION TITLE C-GRID III DUAL ROW KINKED PIN HEADER MOLEX MOLEX EUROPE SHEET NO. 20F DATE 90/09/11 PART NO. SEE CHART DWG NO. SDA-90628 SIZE B											
	10	9	8	7	6	5	4	3	2	1	