








LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			M1	REVISED PER ECO-08-009053	16APR08	DH	AS
			M2	REVISED PER ECO-09-021826	07JAN10	KK	AEG



- 1 HOUSING MATERIAL: LIQUID CRYSTAL POLYMER
COLOR: NATURAL.
- 2 CONTACT MATERIAL: PHOSPHOR-BRONZE.
- 3 CONTACT FINISH:
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL.
ON MATING SURFACES:
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT.
ON LEADS
0.00381 MIN TIN-LEAD OVER UNDERPLATE.
LUBRICATION (ENTIRE CONTACT):
SURFACE CONDITIONER PER AMP SPEC 112-1002 AFTER PLATING.
- 4 PART MARKING LOCATED APPROXIMATELY AS SHOWN.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

6	OBSOLETE	NO	130	65	131.88	3	330	1-223004-1
	OBSOLETE	NO	118	59	119.88	3 3	300	1-223004-0
		NO	106	53	107.88	3	270	223004-9
6	OBSOLETE	NO	94	47	95.88	3 3	240	223004-8
		NO	82	41	83.88	3	210	223004-7
	OBSOLETE	NO	70	35	71.88	3 3	180	223004-6
		NO	58	29	59.88	3	150	223004-5
		NO	46	23	47.88	3 3	120	223004-4
		NO	34	17	35.88	3	90	223004-3
		NO	22	11	23.88	3 3	60	223004-2
		YES	10	3	11.88	3	30	223004-1
	POSITIONING PEGS		C	B	A	FINISH	NO OF SIGNAL POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN R. BUCHHEISTER 07/FEB/96	Tyco Electronics Corporation Harrisburg, Pa 17105-3608		
				CHK D. BAECHTLE 08/FEB/96			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. SINISI 08/FEB/96	NAME		
		0. PLC	± -	PRODUCT SPEC	ASSEMBLY, RECEPTACLE, SIGNAL, RIGHT ANGLE, Z-PACK 2mm FB, 5 ROW, SOLDER LEAD		
		1. PLC	± -				
		2. PLC	± 0.13				
		3. PLC	± -				
		4. PLC	± -	APPLICATION SPEC	-		
		ANGLES	± -				
MATERIAL		FINISH		WEIGHT	RESTRICTED TO		
1 2		3 5		-	-		
CUSTOMER DRAWING				A1 00779 C-223004			
				SCALE 4:1		SHEET 1 OF 1	
						REV M2	

RECOMMENDED CIRCUIT PATTERN
PER IPC-D300 TYPE II, CLASS C
(COMPONENT SIDE)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[223004-4](#)