









mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		BERG ELECTRONICS	
ltr	ecn no	dr	date	linear	.XX ±.01/X ±.3	projection	title	product family	code
A	V81283	EPK	10/19/98		.XXX ±.005/XX ±.13	INCH/MM	RIGHT ANGLE 2 ROW	HEADERS	-
B	V90145	DLH	4/7/99	angles	.XXX ±.0020/XXX ±.051	scale	size	dwg no	sheet
				dr	° ±2°	2:1	A	69922	1 of 3
				enr	E KROPIEWICKI 10/19/98				
				chr	H. SUNDY 10/19/98				
				appd	H. SUNDY 10/19/98				
sheet index	revision	B	B	A					
	sheet	1	2	3					



NOTES:

- THIS LENGTH OF PIN TO BE FREE OF NICKS, TOOL MARKS, AND PLASTIC SLIVERS.
- PIN RETENTION TO BE 3.00 Lbs/1.36 Kgs MIN PER PIN IN EITHER DIRECTION.
- TERMINAL PLATING : SEE PRODUCT TABLE
- MOLDING MAT'L : MIN 20% GLASS FILLED POLYESTER PER UL-94-V0, COLOR: BLACK.
- DIM D =
(NO. OF COLUMNS - 1) TIMES .100 [ENGLISH].
(NO. OF COLUMNS - 1) TIMES 2.54 [METRIC].
- XXX REPRESENTS NO. OF COLUMNS.
(i.e. 2x5 PART IS -005).
-001 THRU -004 ARE NOT AVAILABLE.
-005 THRU -100 ARE AVAILABLE.
- TERMINAL MATERIAL - 3/4 HARD PHOS BRONZE ALLOY UNS C51000.
- "R" SUFFIX ON PART DASH NUMBER INDICATES RETENTION PINS (KINKED). ON PARTS UP TO 2 X 14, RETENTIVE PINS LOCATED ON THE CENTER TWO COLUMNS. ON PARTS 2 X 15 AND ABOVE, RETENTIVE PINS LOCATED ONE COLUMN FROM THE END. (2 PAIR OF PINS ON EACH END)

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	BERG ELECTRONICS title RIGHT ANGLE 2 ROW GUIDE PIN HEADER		
ltr	ecr no	dr	date	linear	angles				
B				.XX ±.01/.3	0° ±2°	projection	product family HEADERS size A code - sheet 2 of		
				.XXX ±.005/.13					
				.XXX ±.0020/.050			69922		
						scale 2:1			
				dr E KROPIEWNICK 10/19/98			cage code 22526		
				engr H. SUNDY 10/19/98					
				chr H. SUNDY 10/19/98					
				appd H. SUNDY 10/19/98					
sheet index	revision sheet								



PRODUCT NO NOTE 6	SIZE NOTE 6	DIM D	DIM F	DIM E	OVERALL LENGTH DIM L	P L A T I N G
69922-XXX	2 x XXX	NOTE 5	.37/9.4 + DIM D	.40/10.2 + DIM D	.48/12.2 + DIM D	15u"/.38u GXT™ OVER 50u"/1.27u Ni
69923-XXX						30u"/.76u GXT™ OVER 50u"/1.27u Ni
69924-XXX						15u"/.38u MIN Au OVER 50u"/1.27 MIN Ni
69925-XXX						30u"/.76u MIN Au OVER 50u"/1.27 MIN Ni
69926-XXX						DUPLEX 30u"/.76u Au & 100u"/2.54u MIN 60/40 SnPb OVER 50u"/1.27 Ni
69927-XXX	2 x XXX	NOTE 5	.37/9.4 + DIM D	.40/10.2 + DIM D	.48/12.2 + DIM D	120u"/3.05u 93/7 SnPb OVER 50u"/1.27u Ni

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY				
ltr	ecn no	dr	date	linear	.xx ±.01/.x ±.3	projection 	title RIGHT ANGLE 2 ROW GUIDE PIN HEADER			
A					.xxx ±.005/.xx ±.13					
					.xxx ±.0020/.xxx ±.051					
				angles	0° ±2°		product family HEADERS size dwg no A 69922			
				dr	E KROPIEWNICI 10/19/98					
				enr	H. SUNDY 10/19/98					
				chr	H. SUNDY 10/19/98	scale 1:1	code sheet 3 of			
				appd	H. SUNDY 10/19/98					
sheet index	revision sheet									