

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	0		D2	REVISED PER ECR-12-010267	05JUN12	JR	TM

- 1


0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.
- 2

WIRE RANGE: 0.05 – 0.15MM² (30–26 AWG).
- 3

INSULATION RANGE: 0.89–1.27[.035–.050] DIA.
- 4

DIMENSIONS IN BRACKETS ARE IN INCHES.
- 5

0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN MATTE TIN IN LOCALIZED TIN PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.



5	0.25[.010] BRASS	1-794216-0
1	0.25[.010] BRASS	794216-3
PRE-TIN	0.25[.010] BRASS	794216-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL 1-15-97	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK R. SWING 1-15-97				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
	0 PLC ± -		PRODUCT SPEC			
	1 PLC ± -		APPLICATION SPEC			
MATERIAL SEE TABLE	2 PLC ± -		SIZE			
	3 PLC ± 0.15 [.006]		CAGE CODE			
	4 PLC ± -		DRAWING NO			
FINISH SEE TABLE		WEIGHT -	A2 00779		C=794216	
CUSTOMER DRAWING			SCALE 10:1		SHEET 1 of 1	
					REV D2	