


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT<br>PART NUMBER | STUD<br>SIZE | DIMENSIONS - in. |               |               |                |               | TOOLS                                                                                                         |
|------------------------|--------------|------------------|---------------|---------------|----------------|---------------|---------------------------------------------------------------------------------------------------------------|
|                        |              | A<br>± .03       | W<br>± .01    | C<br>± .02    | M<br>± .03     | H<br>± .01    |                                                                                                               |
| PV14-6LF               | #6           | .90<br>(22.86)   | .25<br>(6.35) | .22<br>(5.59) | .68<br>(17.27) | .14<br>(3.56) | *CT-100A<br>**CT-600-A (CT-500CH)<br>**CT-600-A (CT-550CH)<br>**CT-1550<br>**CT-1551<br>**CT-2500 (CT-2550CH) |
| PV14-6LFW              | #6           | .90<br>(22.86)   | .29<br>(7.37) | .22<br>(5.59) | .68<br>(17.27) | .14<br>(3.56) |                                                                                                               |
| PV14-8LF               | #8           | .97<br>(24.64)   | .29<br>(7.37) | .25<br>(6.35) | .73<br>(18.54) | .16<br>(4.06) |                                                                                                               |
| PV14-10LF              | #10          | .97<br>(24.64)   | .33<br>(8.38) | .25<br>(6.35) | .73<br>(18.54) | .19<br>(4.83) |                                                                                                               |
| PV14-10LFN             | #10          | .97<br>(24.64)   | .29<br>(7.37) | .25<br>(6.35) | .73<br>(18.54) | .19<br>(4.83) |                                                                                                               |

#### NOTES:

\*USED FOR #16-14 AWG SOLID OR STRANDED COPPER WIRE  
& 167° F (75° C) MAX TEMP. RATING  
 \*\*USED FOR #18-14 AWG SOLID OR STRANDED COPPER WIRE  
& 221° F (105° C) MAX TEMP. RATING

1. cULus LISTED FOR:  
A. 600V MAX. BLDG WIRE  
(1000 V MAX. IN SIGNS, FIXTURES & LUMINARIES)
2. SEE WWW.PANDUIT.COM FOR PACKAGE QUANTITIES
3. MATERIAL:  
A. STAMPING - .032" THK, COPPER  
TIN PLATED  
B. HOUSING - VINYL, BLUE  
C. SLEEVE - BRASS, TIN PLATED
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
5. WIRE STRIP LENGTH:  $5/16 + 1/32$  (7.9 + .8)  
- 0 - 0



|  |  |  |  |  |  |  |                                                                                                |  |             |  |                    |
|--|--|--|--|--|--|--|------------------------------------------------------------------------------------------------|--|-------------|--|--------------------|
|  |  |  |  |  |  |  | TITLE                                                                                          |  |             |  |                    |
|  |  |  |  |  |  |  | #16-14 BARREL FUNNELED VINYL INSULATED LOCKING FORK, .175 [4.45] MAX. WIRE INSULATION DIAMETER |  |             |  |                    |
|  |  |  |  |  |  |  | CUSTOMER DRAWING                                                                               |  |             |  |                    |
|  |  |  |  |  |  |  | ITEM REVISION NAME                                                                             |  | N41296BB/10 |  | <div>PANDUIT</div> |
|  |  |  |  |  |  |  | DATASET FILE NAME                                                                              |  | N41296BB/10 |  |                    |
|  |  |  |  |  |  |  | UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE: IN [ mm ]                           |  |             |  |                    |
|  |  |  |  |  |  |  | .X ±<br>.XX ±<br>                                                                              |  |             |  |                    |