


Data Sheet 2582 Rev. -

R1200F THRU R2000F

HIGH VOLTAGE FAST RECOVERY RECTIFIER

Reverse Voltage - 1200 to 2000 Volts Forward Current - 0.5/0.2 Ampere



Dimensions in inches and (millimeters)

FEATURES

- ◆ The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- ◆ Construction utilizes void-free molded plastic technique
- ◆ Low reverse leakage
- ◆ High forward surge current capability
- ◆ High temperature soldering guaranteed:
250°C/10 seconds, 0.375" (9.5mm) lead length,
5 lbs. (2.3kg) tension

MECHANICAL DATA

Case: JEDEC DO-41/DO-15 molded plastic body

Terminals: Plated axial leads, solderable per MIL-STD-750, Method 2026

Polarity: Color band denotes cathode end

Mounting Position: Any

Weight: 0.012 ounce, 0.33 grams (DO-41)
0.014 ounce, 0.40 grams (DO-15)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

	SYMBOLS	R1200F	R1500F	R1800F	R2000F	UNITS
Maximum repetitive peak reverse voltage	V_{RRM}	1200	1500	1800	2000	VOLTS
Maximum RMS voltage	V_{RMS}	840	1050	1260	1400	VOLTS
Maximum DC blocking voltage	V_{DC}	1200	1500	1800	2000	VOLTS
Maximum average forward rectified current 0.375" (9.5mm) lead length (see fig.1)	$I_{(AV)}$	0.5			0.2	Amp
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	30.0				Amps
Maximum instantaneous forward voltage at 0.5/0.2 A	V_F	2.5			4.0	Volts
Maximum DC reverse current $T_A=25^\circ\text{C}$ at rated DC blocking voltage $T_A=100^\circ\text{C}$	I_R	5.0 50.0				μA
Maximum reverse recovery time (NOTE 1)	t_{rr}	500				ns
Typical junction capacitance (NOTE 2)	C_J	15.0				pF
Typical thermal resistance (NOTE 3)	$R_{\theta JA}$	50.0				$^\circ\text{C/W}$
Operating junction and storage temperature range	T_J, T_{STG}	-65 to +150				$^\circ\text{C}$

Note: 1. Reverse recovery condition $I_F=0.5\text{A}$, $I_R=1.0\text{A}$, $I_{rr}=0.25\text{A}$

2. Measured at 1MHz and applied reverse voltage of 4.0V D.C.

3. Thermal resistance from junction to ambient at 0.375" (9.5mm) lead length, P.C.B. mounted

RATINGS AND CHARACTERISTIC CURVES R1200F THRU R2000F

