


4										3										2										1																																																	
THIS DRAWING IS UNPUBLISHED.										RELEASED FOR PUBLICATION										-										-																																																	
© COPYRIGHT										BY TYCO ELECTRONICS CORPORATION.										ALL RIGHTS RESERVED.																																																											
																				LOC FT										DIST 0										REVISIONS																																							
																				P										LTR										DESCRIPTION										DATE										OWN										APVD									
																														K										REV PER ECO-10-003458										22FEB10										RG										DO									

[.09]	[.016]	B	[.080]	6	12	1-2	0.12	[.005]	--	5-192045-4	OBSOLETE
[.09]	[.016]	B	[.080]	6	12	UNPL	0.12	[.005]	--	5-392045-3	17
[5.98]	[.020]	B	[6.040]	667	12	1-2	0.12	[.005]	05091	5-192045-2	OBSOLETE
[5.98]	[.020]	B	[5.980]	667	12	UNPL	0.12	[.005]	05085	5-192045-1	OBSOLETE
[5.00]	[.020]	B	[5.040]	557	12	1-2	0.12	[.005]	05092	5-192045-0	OBSOLETE
[5.00]	[.020]	B	[4.980]	557	12	UNPL	0.12	[.005]	05084	4-192045-9	OBSOLETE
[4.84]	[.020]	B	[4.880]	539	12	1-2	0.12	[.005]	05093	4-192045-8	OBSOLETE
[4.68]	[.020]	B	[4.660]	521	12	UNPL	0.12	[.005]	05083	4-192045-7	OBSOLETE
[3.38]	[.020]	B	[3.410]	375	12	1-2	0.12	[.005]	05089	4-192045-6	OBSOLETE
[3.22]	[.020]	B	[3.000]	335	12	1-2	0.12	[.005]	--	4-192045-5	OBSOLETE
[3.22]	[.016]	B	[3.000]	335	12	1-2	0.12	[.005]	05086	4-192045-4	OBSOLETE
[2.76]	[.016]	B	[2.750]	305	12	1-2	0.12	[.005]	05073	4-192045-3	OBSOLETE
[2.07]	[.020]	B	[2.100]	228	12	3-2	0.12	[.005]	05090	4-192045-2	OBSOLETE
[1.51]	[.020]	B	[1.500]	166	12	3-2	0.15	[.006]	--	4-192045-1	OBSOLETE
		B	[1.375]	153	13	1-2	0.12	[.005]	05087	4-192045-0	OBSOLETE
[1.13]	[.018]	B	[1.120]	122	12	UNPL	0.12	[.005]	05177	3-192045-9	OBSOLETE
[.97]	[.020]	B	[.950]	105	12	1-2	0.12	[.005]	05094	3-192045-8	OBSOLETE
[.97]	[.020]	B	[.950]	105	12	UNPL	0.12	[.005]	05101	3-192045-7	OBSOLETE
[.95]	[.016]	B	[.938]	102	12	1-2	0.12	[.005]	05074	3-192045-6	OBSOLETE
[.70]	[.016]	B	[.688]	74	12	1-2	0.12	[.005]	05072	3-192045-5	OBSOLETE
[.66]	[.020]	B	[.625]	70	12	3-2	0.15	[.006]	05024	3-192045-4	OBSOLETE
[.67]	[.018]	B	[.598]	71	13	3-2	0.12	[.005]	05178	3-192045-3	OBSOLETE
[.48]	[.020]	B	[.504]	54	12	3-2	0.15	[.006]	05123	3-192045-2	OBSOLETE
[.48]	[.020]	B	[.504]	54	12	1-2	0.15	[.006]	05021	3-192045-1	OBSOLETE
[.48]	[.020]		[.504]	54	12	UNPL	0.15	[.006]	--	3-192045-0	OBSOLETE
									05171	2-192045-9	OBSOLETE
									05170	2-192045-8	OBSOLETE
[.47]	[.016]	B	[.433]	49	12	3-2	0.15	[.006]	05140	2-192045-7	OBSOLETE
[.43]	[.020]	B	[.399]	44	12	3-2	0.12	[.005]	05020	2-192045-6	OBSOLETE
[.39]	[.016]	B	[.375]	39	12	1-2	0.12	[.005]	05076	2-192045-5	OBSOLETE
[.32]	[.020]	B	[.312]	32	12	UNPL	0.12	[.005]	05100	2-192045-4	OBSOLETE
[.27]	[.020]	B	[.250]	26	12	3-2	0.15	[.006]	05017	2-192045-3	OBSOLETE
[.26]	[.016]		[.250]	26		1-2	0.12	[.005]	05071	2-192045-2	OBSOLETE
									05186	2-192045-1	OBSOLETE
[.18]	[.020]	B	[.164]	16	12	3-2	0.15	[.006]	05014	2-192045-0	OBSOLETE
[.18]	[.020]	B	[.164]	16	12	UNPL	0.15	[.006]	05028	1-192045-9	OBSOLETE
[.17]	[.016]		[.156]	14	12	1-2	0.12	[.005]	05075	1-192045-8	OBSOLETE
									05027	1-192045-7	OBSOLETE
[.15]	[.020]	B	[.140]	12	12	6-7	0.10	[.004]	05187	1-192045-6	OBSOLETE
[.15]	[.020]	B	[.140]	12	12	3-2	0.10	[.004]	05166	1-192045-5	OBSOLETE
[.15]	[.020]	B	[.140]	12	12	UNPL	0.10	[.004]	05165	1-192045-4	OBSOLETE
[.14]	[.020]	B	[.125]	11	12	1-2	0.12	[.005]	05096	1-192045-3	OBSOLETE
	[.022]	C	--	15	12	5-2	0.10	[.004]	05119	1-192045-2	OBSOLETE
	[.022]	C	--	14	12	3-2	0.15	[.006]	05002	1-192045-1	OBSOLETE
	[.022]	C	--	14	12	UNPL	0.15	[.006]	05048	1-192045-0	OBSOLETE
	[.018]	C	--	14	12	UNPL	0.15	[.006]	--	192045-9	OBSOLETE
	[.029]	C	--	14	12	1-2	0.12	[.005]	--	192045-8	OBSOLETE
	[.029]	C	--	14	12	UNPL	0.12	[.005]	05185	192045-7	OBSOLETE
	[.022]	C	--	14	12	3-2	0.12	[.005]	--	192045-6	OBSOLETE
	[.022]	C	--	14	12	1-2	0.12	[.005]	05097	192045-5	OBSOLETE
	[.022]	C	--	14	12	UNPL	0.12	[.005]	05055	192045-4	OBSOLETE
	[.018]	C	--	14	12	UNPL	0.12	[.005]	--	192045-3	OBSOLETE
	[.027]	C	--	14	12	3-2	0.10	[.004]	05164	192045-2	OBSOLETE
	[.027]	C	--	14	12	UNPL	0.10	[.004]	05167	192045-1	OBSOLETE

(FREE DIA)	LH	STYLE	MATING DIA	NUM LOUV	MAT'L (NOTE NO)	PLATING	MAT'L THK	REF	PART NUMBER
------------	----	-------	------------	----------	-----------------	---------	-----------	-----	-------------

<

LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN —		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608		
		CHK 08-04-93				
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CONTACT BAND, LAV MALE —		
		J.TURNER				
		APVD —				
		PRODUCT SPEC —				
		APPLICATION SPEC —				
		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL SEE TABLE		FINISH SEE TABLE		A2 00779 C-192045		—
		WEIGHT —		CUSTOMER DRAWING		
				SCALE 1:1		SHEET 2 OF 2
						REV K