

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20



© COPYRIGHT 20

BY -


ALL INTERNATIONAL RIGHTS RESERVED.

REVISIONS



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED (ECR-10-021923)	07.DEC'10	SM	HG






SECTION A-A



ISOMETRIC VIEW



ISO VIEW



SECTION B-B






TABLE 1

P/N : 1897255-2	P/N : 1-1897255-2
APPLICATION PANEL SIZE (THICKNESS : 1.2~1.8 mm)	APPLICATION PANEL SIZE (THICKNESS : 0.7~2.0 mm)

NOTE


1. GENERAL TOLERANCE : ± 0.3 , $\pm 3^\circ$

2. APPLICATION PANEL SIZE : SEE TABLE 1

NO	PART NO.	DESCRIPTION	MATERIAL	COLOR
2	1-1897255-2	SLOT CLIP FOR J300	PA66	BLACK
1	1897255-2	SLOT CLIP FOR J300	PA66	BLACK

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

DWN
SM LEE

CHK
KT LIM

APVD
HG CHO

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

SLOT CLIP FOR J300

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1897255

SCALE 2:1

SHEET 1 OF 1

REV A1