

ADSL LINE TRANSFORMERS

For Centillium ADSL CPE Chipsets



- Matched to Centillium's CopperFlite™ CT-L51ST81, Flite Optimizer™ CT-L52SU81, and Universal CopperFlite™ CT-L61ST81 chipsets
- Excellent THD performance in a small footprint
- Designed to meet UL1950 and EN60950 supplementary insulation requirements for working voltages up to 250 Vrms

Electrical Specifications @ 25°C — Operating Temperature -40°C to +85°C

Part Number	Mounting	Turns Ratio ($\pm 2\%$)	Inductance @ 10 kHz, 100 mV	Leakage Inductance @ 100 kHz, 0.1 Vrms
BX2258	SMT	1CS:1CS (1-5) : (7-10) with (2-4) & (8-9) Shorted	5.0 mH $\pm 10\%$ (7-10) with (8-9) Shorted	15 μ H Max (1-2) with (4-5), (7-10), & (8-9) Shorted
BX2259	SMT	1CS:2.125CS (1-4) : (6-10) with (2-3) & (7-9) Shorted	5.0 mH $\pm 10\%$ (6-10) with (7-9) Shorted	10 μ H Max. (9-10) with (1-4), (2-3), & (6-7) Shorted
BX2353	SMT	1CS:2.125CS (1-4) : (7-10) with (2-3) & (8-9) Shorted	5.0 mH $\pm 10\%$ (7-10) with (8-9) Shorted	13 μ H Max. (7-10) with (1-4), (2-3), & (8-9) Shorted
BX2358	SMT	1CS:1CS (1-4) : (7-10) with (2-3) & (8-9) Shorted	5.0 mH $\pm 10\%$ (7-10) with (8-9) Shorted	15 μ H Max. (7-10) with (1-4), (2-3), & (8-9) Shorted

Additional Electrical Specifications

Part Number	Longitudinal Balance (from 30 kHz to 1.1 MHz)	THD at 100 Ω (@ 30 kHz, 2.5 Vrms)	DC Resistance		Isolation Voltage (1 sec)
BX2258	≤ -40 dB	≤ -85 dB	1.3 Ω MAX (1-2) 1.6 Ω MAX (4-5)	1.5 Ω MAX (7-9) = (8-10)	1,875 Vrms
BX2259	≤ -40 dB	≤ -85 dB	0.35 Ω MAX (1-3) 0.40 Ω MAX (2,4)	1.75 Ω MAX (6-7) = (9-10)	1,875 Vrms
BX2353	≤ -40 dB	≤ -85 dB	0.35 Ω MAX (1-3) 0.40 Ω MAX (2-4)	1.75 Ω MAX (7-9) = (8-10)	1,875 Vrms
BX2358	≤ -40 dB	≤ -85 dB	1.0 Ω MAX (1-3) 1.3 Ω MAX (2-4)	1.1 Ω MAX (7-9) = (8-10)	1,875 Vrms

NOTE: Transformers are shipped in trays unless Tape & Reel packaging is specified by adding the suffix "T" to the part number (i.e. BX2258T).

ADSL LINE TRANSFORMERS


For Centillium ADSL CPE Chipsets




Mechanical

Schematics


BX2XXX




BX2258



BX2259



BX2353/BX2358



Weight6.2 grams
Tape & Reel150/reel
Tray60/tray

Dimensions: $\frac{\text{Inches}}{\text{mm}}$

Unless otherwise specified, all tolerances are $\pm \frac{.010}{0,25}$

For More Information :

UNITED STATES (Worldwide)	UNITED KINGDOM (Northern Europe)	FRANCE (Southern Europe)	SINGAPORE (Southern Asia)	TAIWAN, R.O.C. (Northern Asia)	HONG KONG (China/Hong Kong)	DISTRIBUTOR
12220 World Trade Drive San Diego, CA 92128 U.S.A. http://www.pulseeng.com TEL: 858 674 8100 FAX: 858 674 8262	1 & 2 Huxley Road The Surrey Research Park Guildford, Surrey GU2 5RE United Kingdom TEL: 44 1483 401700 FAX: 44 1483 401701	Zone Industrielle F-39270 Orgelet France TEL: 33 3 84 35 04 04 FAX: 33 3 84 25 46 41	150 Kampong Ampat #07-01/02 KA Centre Singapore 368324 TEL: 65 287 8998 FAX: 65 280 0080	3F-4, No. 81, Sec. 1 HsinTai Wu Road Hsi-Chih, Taipei Hsien Taiwan, R.O.C. Tel: 886 2 2698 0228 FAX: 886 2 2698 0948	19/F, China United Plaza 1008 Tai Nan West Street Cheung Sha Wan, Kowloon Hong Kong, China TEL: 852 2788 6588 FAX: 852 2776 1055	

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners.