


LOC		DIST		REVISIONS					
—		—		P	LTR	DESCRIPTION	DATE	DWN	APVD
					A1	REVISED PER ECO-11-005294	02APR11	RK	HMR


NOTES:

- 1 FOR MINI-APPLICATOR CRIMPING.
- 2 UNDERCOATING:1,25μm Ni,SELECTIVE:0,8μm Au, ZONE 1: 0,5μm MIN. GOLDFLASH.
- 3 UNDERCOATING:1,25μm Ni,SELECTIVE:0,8μm Au, REMAINDER:GOLDFLASH.
- 4 ZONE 1:BRIGHT TIN/LEAD PLATED.
- 5 PRE-TIN PLATED 2,0μm.
- 6 MATERIAL:PHOSPHORBRONZE



TIN	5	167024-3	167021-3
GOLD	3	167024-2	167021-2
GOLD	2	167024-1	167021-1
FINISH		LOOSE PIECE	PARTNUMBER

WIRE RANGE :
0,03-0,09 mm² 28-32 AWG
INSULATION RANGE :
0,5-1,02 DIA. .020-.040 DIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.v.LIEMPT	03 DEC 98	 TE Connectivity			
DIMENSIONS: mm		CHK J.v.LIEMPT	—	NAME AMPMODU MOD.4 RECEPTACLE, S.C.P. STRIP			
		APVD E.LEIJTENS	—				
		PRODUCT SPEC —					
		APPLICATION SPEC —					
MATERIAL —		WEIGHT —		SIZE A3	CAGE CODE 00779	DRAWING NO C-167021	RESTRICTED TO —
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		CUSTOMER DRAWING			SCALE —	SHEET 1 OF 1	REV A1