





REV. 1

DCO 63333

COIL: @ 25°C
 RESISTANCE _____ 25 OHMS ±10%
 NOMINAL VOLTAGE _____ 6.0 VDC
 MUST OPERATE _____ 3.2 VDC

 MUST RELEASE _____ 2.1 VDC MAX, 0.46 VDC MIN.

ENVIRONMENT:

VIBRATION _____ 10 _____ CPS TO _____ 2000 _____ CPS @ _____ 15 _____ g's


SHOCK _____ 100 _____ g's _____ 6 _____ MS. DURATION

TEMPERATURE _____ -65 _____ °C TO _____ +125 _____ °C

NOTES: _____ OPERATE & RELEASE 7 MS MAX.

(INCLUDING BOUNCE)

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: _____ LOW LEVEL TO
 _____ 2 AMP 28 VDC RESISTIVE
 _____ 100,000 OPERATIONS

DR. R.B. 4/20/98

CK. TLG 10-24-00

CII Technologies
 advanced control electronic solutions

CUST. _____ QPL

CUST. NO. _____ M39016/40-006 REV. _____

"SR" RELAY

SR-7606