

CMSZ5221B
THRU
CMSZ5261B

250 mW ZENER DIODE
5% TOLERANCE

SUPERTM
mini



SOT-323 CASE

CentralTM
Semiconductor Corp.

DESCRIPTION:

The CENTRAL SEMICONDUCTOR CMSZ5221B Series Silicon Zener Diode is a high quality voltage regulator for use in industrial, commercial, entertainment and computer applications. Higher voltage devices are available on special order.

ABSOLUTE MAXIMUM RATINGS

Power Dissipation (@ $T_A=25^{\circ}\text{C}$)
Operating and Storage Temperature
Thermal Resistance

SYMBOL

P_D 250
 T_J, T_{stg} -65 to + 175
 Θ_{JA} 500

UNITS


mW
 $^{\circ}\text{C}$
 $^{\circ}\text{C/W}$

ELECTRICAL CHARACTERISTICS ($T_A=25^{\circ}\text{C}$), $V_F=0.9\text{V MAX @ } I_F = 10\text{mA}$ FOR ALL TYPES.

TYPE	ZENER VOLTAGE			TEST CURRENT	MAXIMUM ZENER IMPEDANCE			MAXIMUM REVERSE CURRENT		MAX. TEMP. COEFF.	MARKING CODE
	V _Z @ I _{ZT}										
	MIN	NOM	MAX		I _{ZT}	Z _{ZT} @ I _{ZT}	Z _{ZK} @ I _{ZK}	I _R @ V _R			
	VOLTS	VOLTS	VOLTS		mA	Ω	Ω	mA	μA	VOLTS	
CMSZ5221B	2.280	2.4	2.520	20	30	1200	0.25	100	1.0	-0.085	8A1
CMSZ5222B	2.375	2.5	2.625	20	30	1250	0.25	100	1.0	-0.085	8B1
CMSZ5223B	2.565	2.7	2.835	20	30	1300	0.25	75	1.0	-0.080	8C1
CMSZ5224B	2.660	2.8	2.940	20	30	1400	0.25	75	1.0	-0.080	8D1
CMSZ5225B	2.850	3.0	3.150	20	29	1600	0.25	50	1.0	-0.075	8E1
CMSZ5226B	3.135	3.3	3.465	20	28	1600	0.25	25	1.0	-0.070	8AC
CMSZ5227B	3.420	3.6	3.780	20	24	1700	0.25	15	1.0	-0.065	8BC
CMSZ5228B	3.705	3.9	4.095	20	23	1900	0.25	10	1.0	-0.060	8CC
CMSZ5229B	4.085	4.3	4.515	20	22	2000	0.25	5.0	1.0	±0.055	8DC
CMSZ5230B	4.465	4.7	4.935	20	19	1900	0.25	5.0	2.0	±0.030	8EC
CMSZ5231B	4.845	5.1	5.355	20	17	1600	0.25	5.0	2.0	±0.030	8FC
CMSZ5232B	5.320	5.6	5.880	20	11	1600	0.25	5.0	3.0	+0.038	8GC
CMSZ5233B	5.700	6.0	6.300	20	7.0	1600	0.25	5.0	3.5	+0.038	8HC
CMSZ5234B	5.890	6.2	6.510	20	7.0	1000	0.25	5.0	4.0	+0.045	8JC
CMSZ5235B	6.460	6.8	7.140	20	5.0	750	0.25	3.0	5.0	+0.050	8KC
CMSZ5236B	7.125	7.5	7.875	20	6.0	500	0.25	3.0	6.0	+0.058	8LC
CMSZ5237B	7.790	8.2	8.610	20	8.0	500	0.25	3.0	6.5	+0.062	8MC
CMSZ5238B	8.265	8.7	9.135	20	8.0	600	0.25	3.0	6.5	+0.065	8NC
CMSZ5239B	8.645	9.1	9.555	20	10	600	0.25	3.0	7.0	+0.068	8PC
CMSZ5240B	9.500	10	10.50	20	17	600	0.25	3.0	8.0	+0.075	8QC
CMSZ5241B	10.45	11	11.55	20	22	600	0.25	2.0	8.4	+0.076	8RC
CMSZ5242B	11.40	12	12.60	20	30	600	0.25	1.0	9.1	+0.077	8SC
CMSZ5243B	12.35	13	13.65	9.5	13	600	0.25	0.5	9.9	+0.079	8TC
CMSZ5244B	13.30	14	14.70	9.0	15	600	0.25	0.1	10	+0.082	8UC

TYPE	ZENER VOLTAGE			TEST CURRENT	MAXIMUM ZENER IMPEDANCE			MAXIMUM REVERSE CURRENT		MAX. TEMP. COEFF.	MARKING CODE	
	V _Z @ I _{ZT}											
	MIN	NOM	MAX		I _{ZT}	Z _{ZT} @ I _{ZT}	Z _{ZK} @ I _{ZK}	I _R @ V _R				αV _Z
	VOLTS	VOLTS	VOLTS		mA	Ω	Ω	mA	μA			VOLTS
CMSZ5245B	14.25	15	15.75	8.5	16	600	0.25	0.1	11	+0.082	8VC	
CMSZ5246B	15.20	16	16.80	7.8	17	600	0.25	0.1	12	+0.083	8WC	
CMSZ5247B	16.15	17	17.85	7.4	19	600	0.25	0.1	13	+0.084	8XC	
CMSZ5248B	17.10	18	18.90	7.0	21	600	0.25	0.1	14	+0.085	8YC	
CMSZ5249B	18.05	19	19.95	6.6	23	600	0.25	0.1	14	+0.086	8ZC	
CMSZ5250B	19.00	20	21.00	6.2	25	600	0.25	0.1	15	+0.086	1A8	
CMSZ5251B	20.90	22	23.10	5.6	29	600	0.25	0.1	17	+0.087	1B8	
CMSZ5252B	22.80	24	25.20	5.2	33	600	0.25	0.1	18	+0.088	1C8	
CMSZ5253B	23.75	25	26.25	5.0	35	600	0.25	0.1	19	+0.089	1D8	
CMSZ5254B	25.65	27	28.35	4.6	41	600	0.25	0.1	21	+0.090	1E8	
CMSZ5255B	26.60	28	29.40	4.5	44	600	0.25	0.1	21	+0.091	1F8	
CMSZ5256B	28.50	30	31.50	4.2	49	600	0.25	0.1	23	+0.091	1G8	
CMSZ5257B	31.35	33	34.65	3.8	58	700	0.25	0.1	25	+0.092	1H8	
CMSZ5258B	34.20	36	37.80	3.4	70	700	0.25	0.1	27	+0.093	1J8	
CMSZ5259B	37.05	39	40.95	3.2	80	800	0.25	0.1	30	+0.094	1K8	
CMSZ5260B	40.85	43	45.15	3.0	93	900	0.25	0.1	33	+0.095	1L8	
CMSZ5261B	44.65	47	49.35	2.7	105	1000	0.25	0.1	36	+0.095	1M8	

All dimensions in inches (mm).



NO
CONNECTION

