

SMT Power Inductor




HAH1340 Type

Features


- Low profile (4.0mm max. height) SMD type.
- Magnetically shielded, suitable for high density mounting.
- High energy storage and low DCR.
- Provided with embossed carrier tape packing.
- Ideal for power source circuits, DC-DC converter, DC-AC inverters inductor application.
- In addition to the standard versions shown here, customized inductors are available to meet your exact requirements.



Mechanical Dimension:



RECOMMENDED PAD



UNIT : mm / inch
 A = 13.0 ± 0.5 / 0.512 ± 0.020
 B = 12.7 ± 0.4 / 0.500 ± 0.016
 C = 2.4 / 0.094
 D = 4.0 / 0.157 Max.
 E = 0.03 / 0.001
 F = 3.0 / 0.118

Electrical Characteristics: At 25°C: 100KHz, 1V

PART NO.	Lo (μ H) Typ.	Li ¹ (μ H) $\pm 20\%$	DCR (m Ω) MAX	Isat (Amperes)
HAH1340-0R2	0.25	0.20	0.80	40
HAH1340-0R6	0.60	0.50	2.50	30
HAH1340-1R2	1.20	1.00	3.45	22
HAH1340-1R8	1.80	1.60	12.00	12
HAH1340-2R7	2.70	2.40	14.00	10

1. Li is the inductance at Isat

2. Operating temperature: -20°C to 105°C (including self-temperature rise)



DELTA ELECTRONICS, INC.

(TAOYUAN PLANT CPBG) 252, SAN YING ROAD, KUEISAN INDUSTRIAL ZONE, TAOYUAN SHIEN, 333, TAIWAN, R.O.C.

TEL: 886-3-3591968; FAX: 886-3-3591991

<http://www.deltaww.com>