


- NOTES:
- 1.0 ELECTRICAL SPECIFICATIONS
 - 1.1 FREQUENCY RANGE:DC to 12.4 GHz
 - 1.2 MAXIMUM INPUT POWER:
 - AT +25°C: 2 WATTS
 - AT +125°C: 0.5 WATTS
 - 1.3 OPERATING TEMPERATURE RANGE:
 - 55°C to +125°C
 - 1.4 IMPEDANCE: 50 OHMS
 - 1.5 MAXIMUM VSWR:
 - DC to 4.0 GHz: 1.07:1
 - 4.0 to 12.4 GHz: 1.12:1

- 2.0 MARK UNIT AS SHOWN.
- 3.0 DIMENSIONS IN PARENTHESIS ARE MILLIMETERS.



DWG NO. WAS: 02357-01-00

REV.	DESCRIPTION	DATE
-	RELEASED	3/21/92
A	ECR 6545	6/27/89
A1	REDRAW ON CAD-UPDATE	3/27/92
	MARKING. ADD SPECS.	
B	ECN 12868	8/23/93
C	ECN 13622	5/16/94
C1	ADDED TITLEBLOCK	10/26/05
F	ECO 23134	1/3/11

NOTICE: The information contained in this drawing is proprietary and must not be used without the permission of Emerson Network Power.

UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES AND TOLERANCES ARE:

3 PLACE DECIMALS ±.005

2 PLACE DECIMALS ±.02

FRACTIONS ±1/64

PARALLELITY: T.I.R. _____

FLATNESS: T.I.R. _____

CONCENTRICITY: T.I.R. _____

ANGLES AND PERPENDICULARITY: ±1°

CAGE CODE

34078

**EMERSON**
Network Power
Connectivity Solutions

DRAWN/DATE

A.BEATTY
3/27/92

CHECKED/DATE

ENG./DATE

G.KOZAK
3/30/92

APPROVED/DATE

TITLE

TERMINATION
OUTLINE DRAWING

DRAWING NUMBER

TRM-2053-MC-NNN-02-01

SCALE:

5=1

SHEET

1

of

1

REV.

F