

	TECHNICAL DATA SHEET		code	YE00819
			version	1
	EIB cable 2x0.8B PVC FS PVC		date	2008-06-30
			page	1/2

APPLICATION

EIB cable for building management.

CONSTRUCTION



1. Conductor

Diameter of conductor
Material

0.8 mm (0.5mm²)
solid bare copper

2. Insulation

Material
Diameter over insulation
Wallthickness

PVC
1.40 ± 0.05 mm
0.3 mm

3. Overall Cabling

Colour code

red –black
Cable core is wrapped with a PET
or PP foil (overlap > 15%)
< 80 mm

Laylength

4. Outer shield

Shield
Shield Material
Shield Thickness Alu
Shield coverage
Drainwire

Beldfoil®)
Aluminium / Polyester tape
9 µm
100%
0.4 mm Solid tinned Cu

5. Sheath

Material
Colour
Nominal thickness
Nominal diameter
Cable has a round appearance, sheath easy to remove.

PVC (RAL 6017)
Green
1.2 mm
5.5 mm +/- 0.3 mm

	TECHNICAL DATA SHEET		code	YE00819
			version	1
	EIB cable 2x0.8B PVC FS PVC		date	2008-06-30
			page	2/2

REQUIREMENTS AND TEST METHODS

Electrical:

Maximum resistance conductor	34 Ω /km
Maximum capacitance conductor-conductor	100 nF/km
Testvoltage conductor-conductor	1000 VDC, 1 min.
Testvoltage conductor-screen	1000 VDC, 1 min.

Mechanical and physical:

Flame resistance	IEC 60332-1
Temperature range processing and operating	-20 to +70 °C
Temperature range storage	-30 to +70 °C
Minimum bending/setting radius	5*D/10

Cableprint: (in black ink) once every meter.

(WW/YY week and yearnr of production, xxxx M = metermarking)

“BELDEN (TM) YE00819 EIB 1X2X0.8 MM WW/YY xxxx M REG NR. 109/7253/05”



Belden CDT believes this product to be in compliance with the environmental regulations EU RoHS (Directive 2002/95/EC, 27 January 2003); this is valid for all material produced after the RoHS compliant date for this product.