




Copyright FCI.



NOTES
1. SPECIFICATIONS
Current Rating: 1A AC,DC
Voltage Rating: 125V AC,DC
Temperature Range: -40°C ~ +105°C
Contact Resistance: 20mΩ Max.
Insulation Resistance: 100MΩ Min.
Withstanding Voltage: 500V AC/minute
2. Material & Finish:
Housing: Natural Thermoplastic, UL94V-0
Contact and metal hold-down: Phosphor Bronze
Plating of contact: Matte Tin or gold plating over Nickel
Plating of metal hold-down: Matte Tin over Nickel
3. Crimping application hand tool P/N: 10118656-1000
4. Ordering Information & Dimensions:
10114828- X X X XX X LF
Material: LCP
1: LCP
Plating: 0: Matte Tin
1: Gold Flash
3: Gold 30u"
LF: See note A
VOID: NORMAL
1: SEE SHEET 2 (VOID 2&4 PIN)
pin counts from 02~15
Packaging:
1: Tape & Reel
2: Tape & Reel+ Cap(sheet 2)

Part No.	Dimensions					
	POS	A	B	C	D	E
10114828-xxx02LF	2	4.25	1.25±0.10	4.94	3.05	7.25
10114828-xxx03LF	3	5.50	2.50±0.10	6.19	4.30	8.50
10114828-xxx04LF	4	6.75	3.75±0.10	7.44	5.55	9.75
10114828-xxx05LF	5	8.00	5.00±0.10	8.69	6.80	11.00
10114828-xxx06LF	6	9.25	6.25±0.15	9.94	8.05	12.25
10114828-xxx07LF	7	10.50	7.50±0.15	11.19	9.30	13.50
10114828-xxx08LF	8	11.75	8.75±0.15	12.44	10.55	14.75
10114828-xxx09LF	9	13.00	10.00±0.15	13.69	11.80	16.00
10114828-xxx10LF	10	14.25	11.25±0.20	14.94	13.05	17.25
10114828-xxx11LF	11	15.50	12.50±0.20	16.19	14.30	18.50
10114828-xxx12LF	12	16.75	13.75±0.20	17.44	15.55	19.75
10114828-xxx13LF	13	18.00	15.00±0.20	18.69	16.80	21.00
10114828-xxx14LF	14	19.25	16.25±0.20	19.94	18.05	22.25
10114828-xxx15LF	15	20.50	17.50±0.20	21.19	19.30	23.50

Note A: The LF means RoHS compliance, the housing will withstand exposure to peak temperature 260 degree C for 5 sec in the IR re-flow process.

ITEM	MATERIAL	DESCRIPTION
1	THERMOPLASTIC HIGH TEMPERATURE	HOUSING
2	COPPER ALLOY	TERMINAL
3	COPPER ALLOY	HOLD DOWN

rev	ecn no	dr	date
A	T10-0145	J H	12/1/10
H	ELX-N-17075	TIM	2014/04/28
J	ELX-N-17516	TIM	2014/04/21

www.fciconnect.com			surface 6.4 / tolerance std ISO 1302 ✓ ISO 406 ISO 1101		projection 		MM 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED					
Dr	JASON HSU	12/1/10	ANGULAR	LINEAR	0.X	±0.25	size A4	Scale 1.000
Eng	JASON HSU	12/1/10			0.XX	±0.15		
Chr	GARY HSIEH	12/1/10	0°	±2°	0.XXX	-	ECN	
Appr	JOSEPH HSIA	12/1/10	Product family WTB				Spec ref	
		title WTB 1.25MM WAFER 180° SMT				dwg no 10114828		Rev. J
		catalog no				CUSTOMER		sheet 1 of 2

REV F - 2006-04-17

1

2

3

4

A

B

C

D






A

B

A

C

D

ASSEMBLY CAP

10114828-XXXXX1LF

Copyright FCI.

www.fciconnect.com			surface 6.4 ISO 1302	tolerance std ISO 406 ISO 1101	projection ISO 1101	MM
TOLERANCES UNLESS OTHERWISE SPECIFIED			ANGULAR	LINEAR	size A4	Scale 1.000
Dr	JASON HSU	12/1/10	0°	±2°	0.X ±0.25	ECN
Eng	JASON HSU	12/1/10	0.XX ±0.15			
Chr	GARY HSIEH	12/1/10	0.XXX -			
Appr	JOSEPH HSIA	12/1/10	Product family WTB		Spec ref	
FCI			title WTB 1.25MM WAFER 180° SMT		dwg no 10114828	Rev. J
			catalog no		CUSTOMER	sheet 2 of 2

REV F - 2006-04-17

1

2

3

4

PDS: Rev :J

STATUS:Released

Printed: Apr 25, 2014