





FCIconnect.com

Copyright FCI

PRODUCT NUMBER
51110-1096FB




mat'l. code				surface	tolerance	projection	product family
				ISO 1302	ISO 406 ISO 1101		HPC
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM scale 1:1	title
A	V80432	MSC	3/17/98	angles	linear .XX $\pm$.01/.3		4 ROW R/A RECEPT.
B	V00261	JWS	1/24/00	0 $\pm$ 2'	linear .XXX $\pm$.005/.13		P.F., 0 G.P., 5 C.P.
C	M06-0255	AGS	7/6/06		linear .XXX $\pm$.0020/.051		
				dr	M. CLOUSER 3/17/98	FCI	dwg no
				enr	J. BROWN 3/17/98		sheet 1 of 2 size
				chr	J. BROWN 3/17/98		51110 A3
				appd	J. BROWN 3/17/98		type Product Customer Drawing
sheet index	revision sheet	C	C				




FCIconnect.com

Copyright FCI


PRODUCT NUMBER
51110-1096FB




SECTION U-U



SECTION Y-Y



SECTION X-X



NOTES:

1. PRODUCT NUMBERING CODE:
51110- 1 096 F B
SPECIAL FEATURE (NOTE 10)
TAIL LENGTH (NOTE 4)
NO. OF POSITIONS
PLATING (NOTE 3)
BASE NUMBER
2. HOUSING MATERIAL: GLASS AND MINERAL FILLED HIGH TEMP. THERMO PLASTIC. FLAME RETARDANT PER UL94V-0.
COLOR: BLACK.
CONTACT MATERIAL: BeCu
3. PLATING CONTACT AREA:
1 = 30u"/.76u GOLD
COAX PLATING:
50u"/1.27u Ni UNDER 30u"/0.76u Au IN CONTACT AREA.
50u"/1.27u Ni ALL OVER ON MOUNTING BLOCK.
4. TAIL LENGTH:
F = .145 ± .010 / 3.68 ± .25
ALL COAX TAILS = .145 / 3.68
5. $\phi .0453/1.151$ DRILLED HOLE PLATED WITH .0003/.007 MIN. SnPb OVER .001/.03 to .003/.08 Cu. PLATING TO ACHIEVE A $\phi .040 \pm .003/1.02 \pm .08$ HOLE.
6. MANUFACTURE'S NAME, PART NUMBER AND LOT CODE TO APPEAR ON THIS SURFACE PER BUS-12-108.
7. FOR DOCUMENTATION MENU, SEE SPECIFICATION BUS-01-057.
8. USE INSTALLATION TOOL P/N (T.B.D.)
9. SEE 51109 FOR MATING CONNECTOR.
10. SPECIAL FEATURE:
"B" = PRE-INSTALLED EYELET FOR P.C.B. ATTACHMENT IN A $\phi .100$ MOUNTING HOLE.
11. PARTS CAN BE CONFIGURED WITH EITHER R/A COAX P/N 51120-001 OR CABLE COAX P/N 51120-002. PARTS ARE CONFIGURED WITH R/A COAX UNLESS OTHERWISE SPECIFIED.

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ecn	no	dr	date	tolerances unless otherwise specified	scale 1:1	title
c					angles linear .XX ± .01/.3 0' ± 2' .xxx ± .005/.13 .xxx ± .0020/.051		4 ROW R/A RECEPT. P.F., 0 G.P., 5 C.P.
			dr	M. CLOUSER	3/17/98	FCI	dwg no
			enr	J. BROWN	3/17/98		sheet 2 of 2 size
			chr	J. BROWN	3/17/98		51110 A3
			appd	J. BROWN	3/17/98		type Product Customer Drawing
sheet index	revision	sheet					

form: A3