



8467




8467-0-15-XX-21-XX-04-0
Hex press-fit in 0,91 plated thru hole

6192




6192-0-15-XX-21-XX-04-0
Square press-fit in 0,81 plated thru hole

9553




9553-0-15-XX-X1-XX-04-0
Hex press-fit in 1,04 plated thru hole

5531




5531-0-15-XX-21-XX-10-0
Hex press-fit in 1,04 plated thru hole

7553




7553-0-15-XX-11-XX-10-0
Hex press-fit in 1,04 plated thru hole

9407




9407-0-15-XX-11-XX-10-0
Solder mount in 1,02 min. mounting hole

9462




9462-0-15-XX-21-XX-04-0
Hex press-fit in 1,09 plated thru hole

1147




1147-0-18-XX-21-XX-10-0
Press-fit in 1,09 min. mounting hole
Accepts wire sizes up to 0,36 Dia.

3061




3061-0-19-XX-21-XX-10-0
Wire Crimp Termination. Accepts wire sizes 28 AWG Max. / 32 AWG Min.

0579




0579-0-15-XX-X1-XX-10-0
Press-fit in 1,02 mounting hole

8874



8874-0-15-XX-11-XX-10-0
Bottom entry
Surface mount

0613



0613-0-15-XX-21-XX-10-0
Press-fit in 1,19 mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: $\pm 0,13$
DIAMETERS: $\pm 0,05$
ANGLES: $\pm 2^\circ$

ORDER CODE: XXXX - X - 1X - XX - XX - XX - 10 - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 5,08 μ m TIN/LEAD OVER NICKEL
- 80 5,08 μ m TIN OVER NICKEL (RoHS)
- 15 0,25 μ m GOLD OVER NICKEL (RoHS)



SPECIFY CONTACT FINISH:

- 02 2,54 μ m TIN/LEAD OVER NICKEL
- 84 2,54 μ m TIN OVER NICKEL (RoHS)
- 27 0,76 μ m GOLD OVER NICKEL (RoHS)

SELECT CONTACT

#11 or #21 CONTACT (DATA ON PAGE 217)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[7553-0-15-01-11-02-10-0](#) [7553-0-15-01-11-27-10-0](#) [7553-0-15-80-11-84-10-0](#) [7553-0-15-80-11-27-10-0](#)