



Ø16.00
[.630 in]



PANEL CUTOUT
MAX. PANEL THICKNESS
14.0mm [.55]

SWITCH FUNCTION	
POS. 1	POS. 2
ON	(ON)
1-3	1-2

(ON) = MOMENTARY



Ø18.00
[.71 in]

Ø10.40
[.41 in]

Ø12.00
[.472 in]

▲ RING ILLUMINATION
COLOR: BLUE

▲ HIGH ACTUATOR
POLISHED STAINLESS STEEL

▲ BODY
POLISHED STAINLESS STEEL



3.9±.50
[.154±.020 in]

1.50
[.06 in]

18.5±1.0
[.73±.04 in]

30.2±1.0
[1.19±.04 in]

▲ 37.1±1.0
[1.46±.04 in]

2.00
[.079 in]

36.0±1.0
[1.42±.04 in]

.80
[.031 in]

1.80
[.071 in]

2.50
[.098 in]


LED 1 (+)

TERMINAL 3

TERMINAL 2

TERMINAL 1

LED 2 (-)



M16x1.0

.40
[.016 in]

2.80
[.110 in]

5.60
[.220 in]

9.00
[.354 in]

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ±0.4
X.XX = ±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER
5. RATING: 1A 24VDC
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MΩ MIN.
8. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
9. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
10. OPERATING TEMP.: -20°C to 55°C
11. ▲ DENOTES CRITICAL PARAMETER.
12. HARDWARE SUPPLIED: O-RING AND HEXNUT
13. INGRESS RATING: IP40
14. 2011/65/EU (ROHS) COMPLIANT
15. LAMP VOLTAGE: 125V



E-SWITCH®

D	22882	UPDATED RATING TO 1A 24VDC	6/7/17	MJR
C	22107	UPDATE TO NEW TERMINAL HOUSING	12/28/15	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PV3H2B0SS-346

SCALE 3:2

DATE 12/27/2012

DR EBP

DWG 52-PV3H2B0SS346

REV D