

APPLICATOR PARTS LIST

TYPE

HINGE-BAR MARK III (L.H.)

 AMP INCORPORATED
HARRISBURG, PENNA.

NO.	DESCRIPTION	REQ.	PART NO.	NO.	DESCRIPTION	REQ.	PART NO.	CRIMPING DATA				TERMINALS
1	■ WIRE CRIMPER	1	460028-3	42	FRONT STAB. BAR	1	811006-1	TO APPLY TERMINAL				62057-4
2	■ INS. CRIMPER			43				SPEC 114-2078				
3	■ ANVIL	1	843101-1	44	HINGE BLOCK & STAB.	1	811444-1	WIRE SIZE	CRIMP HEIGHT			
4	ANVIL INSERT INSERT	1	460027-1	45	HINGE PIN	1	811007-1	12	.069			
5	■ SHEAR BLADE	1	460026-1	46	GUARD, FRONT STAB.	1	811040-1	10	.085			
6	■ REAR SHEAR PLATE	1	460025-1	47	HINGE BAR ASS'Y	1	565098-1					
7	SHEAR BLADE SPRING SPRING	1	810410-1	48	HINGE BAR SPRING	2	3-23846-5					
8	■ FRONT SHEAR PLATE	1	388632-5	49	STRIP GUIDE STOP	2	810417					
9	REAR ANVIL SPACER PLT.			50	STRIP HOLD DOWN			CRIMP	SIZE	TYPE	FEED	
10	FRONT ANVIL SPACER PLT.			51	SPACER COMP. SPRING	2	811070-1	WIRE	200	TL		
11	TOOL SPACER			52	CAM FOLLOWER HOLDER	1	810409-1	INSUL.	-H	-H	.760	
12	CRIMP SPACER			53	CAM FOLLOWER	1	24746-1	SLEEVED	-H	-H		
13	FRONT STRIP GUIDE	1	811566-2	54	SPRING BRACKET	1	810418	INSULATION RANGE		WIRE RANGE		
14	REAR STRIP GUIDE	1	460023-3	55	CAM FOLLOWER SPRING ■	1	810408	-H-		12-10		
15	RAM	1	811450-1	56	HOOK HOLDER	1	811442-1	EXPLODED VIEW				
16	RAM RAM RET. PL.	1	465004-2	57	SHEAR PICK-UP HOOK ■	1	811443-1	A-6004-5 A-6004-6				
17	ADJ. PLATE PLATE	1	811010-1	58	HOLD DOWN-HINGE BAR	1	811009-1	REMARKS:				
18	PROTECTIVE PLUG PROTECTIVE PLUG	1	23141-1	59	DEPRESSOR SCREW	1	810842-1	LEFT-HAND				
19	APPLICATOR MOUNT ASSY.			60	WASHER	4	376482	△ ITEMS 68 & 72 MOUNT TO REEL SUPPORT SHAFT TO SUPPORT TERMINAL REEL. △ FOR TERMINAL 62057 PRIOR TO REV Z, USE ANVIL P/N 692901-1 ■ DENOTES WEARING PARTS RECOMMEND PURCHASE REPLACEMENT				
20	BASE PLATE	1	465408-1	61	FEED FINGER SPRING ■	1	810421-1					
21	BASE BLOCK			62	DOWEL PIN	2	1-21030-5					
22	STRIP GUIDE PLATE			63	MICRO-SWITCH	1	23496-1					
23	ANVIL HOLDER	1	811445-1	64	MICRO-SWITCH COVER	1	22689-2					
24	AUX. ANVIL HOLDER			65	BRACKET, MICRO-SWITCH	1	811074-1					
25	STRIPPER			MISCELLANEOUS								
26	STRIPPER MOUNT			66	CONNECTOR	1	22787-2					
27	RETAINER PLATE			67	HOOK HOLDER SCREW	1	810413					
28	STRIPPER MOUNT BRACKET			68	SCR. SOC. HD CAP 1/4-20x1.00	2	21001-6					
29	STRIPPER BUSHING			69	SPACER (ANVIL HOLDER)	1	811223-1					
30	STOCK DRAG	1	460024-1	70	LEAD WIRE	1	465918-1					
31	STOCK DRAG HANDLE			71	DOWEL PIN	1	465702-1					
32	STOCK DRAG STUD			72	WASHER, BEVELED	2	682131-1					
33	STOCK DRAG SPRING	2	810135	REV.	REVISION RECORD	DATE	BY	ECN				
34	STOCK DRAG ADJ. SCREW			A	REV PER ECN	7-29-78	KS	R2629				
35	FEED FINGER HOLDER	1	810131	B	ADD ITEMS 68 & 72	11/13/78	LE	R2752				
36	FEED FINGER	1	811440-2	C	ECN A-095188	6-23-88	JS	-				
37	FEED FINGER TIP	1	811439-1	D	ECN A-368692	6-2-92	JUL	-				
38	FEED FINGER STUD STUD	1	810414-1	DI	ECN 0150-1142-04	8-04	MY	TE				
39	BASE CASTING	1	811451-1									
40	GUARD	1	461100-1									
41												

 THIS APPLICATOR IS TO BE USED ON
AMP-O-LECTRIC 1-471273-3
AMP-O-MATIC

SERIAL NO.	DATE SHIPPED	DESIGNED
CUSTOMER NAME AND ADDRESS	CHK'D	5-26-78
THIS DRAWING IS A CONTROLLED DOCUMENT	APP'D.	5-78
APPLICATOR NUMBER	REV.	DI 566276-1
		SHEET 1 OF 1

CUSTOMER AND ASSEMBLY DRAWING

RESTRICTED TO

FOR HARDWARE SEE 687520-9

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[566276-1](#)