

1-1825289-0 Product Details

[Share](#) [Print](#) [Email](#)


1-1825289-0
(MHS233K04)

TE Internal Number: 1-1825289-0

 [Active](#)

Slide Switches

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- 3 Positions
- Double Pole - Three Throw Configuration (Pole-Throw)
- Actuator Style = Lever
- Actuator Color = Black
- MHS Series

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [SLIDE SWITCH, MHS SERIES, DOUBLE POLE, VERTICAL](#) (PDF, English)

Catalog Pages/Data Sheets:

- [SWITCHES CORE PROGRAM CATALOG](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Configuration (Pole-Throw) = Double Pole - Three Throw
- Actuator Style = Lever
- Series = MHS
- Mount Angle = Vertical
- Terminal Configuration = Standard
- Grade = Instrumentation
- Termination Type = PC
- PCB Mount Retention = With

Electrical Characteristics:

- Contact Rating = 300mA

Body Features:

- [Number of Positions](#) = 3
- Actuator Color = Black
- Mount Style = Through-Hole
- Switch Style = Low Profile
- PCB Tail Length (mm [in]) = 3.51 [0.136]
- PCB Mount Retention Type = Guide Posts
- Actuator Length (mm [in]) = 4.50 [0.117]
- Actuator Material = Thermoplastic
- Actuator Travel = 2.00 [.079]

Contact Features:

- Contact Plating = Silver
- Contact Base Material = Copper Alloy

Housing Features:

- UL Flammability Rating = UL 94-HB

Configuration Features:

- Operating Function = On On On
- Number of Actuators = Single

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Identification Marking:

- Stamped Marking = With

Other:

- Brand = Alcoswitch

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

