

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [76410-1808](#)
Status: **Active**
Overview: [Impact™ Backplane Connector and Cable Assembly System](#)
Description: Impact™ 100 Ohm 3 Pair Right Angle Male Header, Unguided, Open Endwall, 8 Columns, 72 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free

Documents:
[3D Model](#) [Application Specification AS-76060-990 \(PDF\)](#)
[Drawing \(PDF\)](#) [Application Specification AS-76060-994 \(PDF\)](#)
[Product Specification PS-76060-999 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family Backplane Connectors
Series [76410](#)
Application Coplanar
Application Tooling Documents TM-622018799
Component Type PCB Header
Overview [Impact™ Backplane Connector and Cable Assembly System](#)
Product Name Impact™
Style N/A
UPC 884982471290

Physical

Circuits (Loaded) 72
Circuits (maximum) 72
Color - Resin Black
Durability (mating cycles max) 200
First Mate / Last Break No
Flammability 94V-0
Guide to Mating Part No
Keying to Mating Part None
Material - Metal High Performance Alloy (HPA)
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Net Weight 6.241/g
Number of Columns 8
Number of Pairs 3
Number of Rows 9
Orientation Right Angle
PC Tail Length 1.20mm
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.00mm
Packaging Type Tray
Pitch - Mating Interface 1.90mm
Pitch - Termination Interface 1.90mm
Plating min - Mating 0.762µm
Polarized to PCB No
Temperature Range - Operating -55°C to +85°C
Termination Interface: Style Through Hole - Compliant Pin



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS

Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[76410Series](#)

Mates With
76170 Impact™ 100 Ohm 3 Pair Right Angle Daughtercard

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Daughter Card	0622018646
Module Installation	
Press-In Tool for 3-Pair by 10-Column Assemblies	
Daughter Card	0622018675
Module Installation	
Press-In Tool for 3-Pair by 8-Column Assemblies	

Electrical

Current - Maximum per Contact	0.75A
Data Rate	25.0 Gbps
Impedance	100#
Shield Type	N/A
Shielded	No
Voltage - Maximum	30V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-76060-990, AS-76060-994
Product Specification	PS-76060-999
Sales Drawing	SD-76410-001
Symbol/Footprint Data	SYM-76410-1808

Impact™ Right Angle0622024350
Module Removal
Tool (RAM)

This document was generated on 09/23/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION