



MATERIALS AND FINISHES

BODY BRASS
PLATED GOLD

CENTER CONTACT BERYLLIUM COPPER
PLATED GOLD

INSULATOR TEFLON



PS-89675-1920	ELECTRO/MECH PERFORM.
SPECIFICATION	DESCRIPTION

73415-2064	73415-2061. ONE PER BAG
73415-2063	73415-2061 WITH TAPE & REEL
73415-2062	73415-2060 WITH TAPE & REEL
73415-2061	PER COMMERCIAL REQUIREMENTS
73415-2060	PER MILITARY REQUIREMENTS
PART NO.	PLATING

OPTION 1 PCB LAYOUT

OPTION 2 PCB LAYOUT

ADDED COPLANARITY
DIMENSION
PER RF14-E057

EC NO: URF2014-0306
DRAWN IN 2013/11/14
CHKD: JAPPR:HUANG
REV: 2014/02/13

QUALITY
SYMBOLS
▽=0
▽=0
▽=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .0002
3 PLACES	± .005	± .0002
2 PLACES	± .005	± .0002
1 PLACE	± .005	± .0002
0 PLACE	± .005	± .0002

ANGULAR ± 2 °
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY	DATE
TEF	2000/04/18

CHECKED BY	DATE
SSS	2000/04/18

APPROVED BY	DATE
GMH	2000/04/18

MATERIAL NO.
SEE TABLE

SCALE
DESIGN UNITS
METRIC



THIRD ANGLE
PROJECTION

MMCX JACK, VERTICAL
PCB/SMT 50 OHMS
MMCX-J/PCB


molex

DOCUMENT NO.
SD-73415-206

SHEET NO.
1 OF 4



SECTION Z-Z



SECTION Y-Y

SEE SHEET 1
EC NO: URF2014-0306
2013/11/14
CHKD: DRWNLIN
APPR: MUANG
2014/02/13

QUALITY SYMBOLS
▽=0
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± ---	± ---
1 PLACE	± ---	± ---
0 PLACE	±	±

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY	DATE
TEF	2000/04/18

CHECKED BY	DATE
SSS	2000/04/18

APPROVED BY	DATE
GMH	2000/04/18

MATERIAL NO.

SEE SHEET 1

SCALE

DESIGN UNITS
METRIC

THIRD ANGLE PROJECTION

TITLE

MMCX JACK, VERTICAL
PCB/SMT 50 OHMS
MMCX-J/PCB

molex

DOCUMENT NO.


SD-73415-206

SHEET NO.





2 OF 4

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

NOTE:
13" REEL SIZE FOR 1600 PIECES



SEE SHEET 1 EC NO.: URF2014-0306 2013/11/14 DRWN:LIN CHKD: APPR:MHUANG 2014/02/13 A9	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		= 0	4 PLACES	± ---	± ---	DRAWN BY	DATE	TITLE MMCX JACK, VERTICAL PCB/SMT 50 OHMS MMCX-J/PCB molex			
		= 0	3 PLACES	± ---	± ---	CHECKED BY	DATE				
		= 0	2 PLACES	± ---	± ---	SSS	2000/04/18				
			1 PLACE	± ---	± ---	APPROVED BY	DATE				
			0 PLACE	±	±	GMH	2000/04/18				
		ANGULAR ± 2 °				MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SEE SHEET 1		SD-73415-206		3 OF 4	
						SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
						C					



PART NO.
73415-2062/73415-2063

1600 SET PER 13" REEL

8000 CONNECTORS PER
OUTER CARTON BOX
339 X 339 X 100 REF.

SEE SHEET 1 EC NO: URF2014-0306 2013/11/14 DRAWN: LIN CHKD: APPR: HUANG 2014/02/13	DESCRIPTION REV	QUALITY SYMBOLS 	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
												MMCX JACK, VERTICAL PCB/SMT 50 OHMS MMCX-J/PCB molex
			4 PLACES	±	---	±	---	DRAWN BY	DATE	TITLE		
			3 PLACES	±	---	±	---	CHECKED BY	DATE			
			2 PLACES	±	---	±	---	SSS	2000/04/18			
			1 PLACE	±	---	±	---	APPROVED BY	DATE			
			0 PLACE	±		±		GMH	2000/04/18			
			ANGULAR ± 2 °			MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE SHEET 1		SD-73415-206		4 OF 4		
						SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				