





- 1 MATERIAL:
BODY: BRASS PER ASTM-B-19
SLEEVE: STAINLESS STEEL PER ASTM-A-240.
- 2 FINISH: .000030 MIN THK GOLD PER ASTM-B-488
OVER .000050 MIN THK NICKEL PER AMS-QQ-N-290.
- 3 FINISH: SELECTIVE .000030 MIN THK GOLD PER ASTM-B-488
OVER .000050 MIN THK NICKEL PER AMS-QQ-N-290.
- 4 FINISH: .000150 MIN TIN OVER NICKEL FLASH.
CAUTION: USE OF TIN PLATED TERMINALS IN CERTAIN
ENVIRONMENTAL MAY CAUSE NON-CONFORMANCE TO TYCO
PRODUCT SPECIFICATION 108-10015.
5. WIRE RANGE: 20, 22 & 24 AWG
INSULATION RANGE: .062 MAX.
HAND CRIMPING TOOL: TYCO P/N 90260-1
EXTRACTION TOOL: TYCO P/N 91038-3
INSERTION TOOL: TYCO P/N 91042-1
6. PART NUMBERS 203816-7 THRU 1-203816-6 ARE OBSOLETE.

	LOOSE PIECE			203816-6
	ON STRIP			203816-5
	LOOSE PIECE			203816-4
OB S OLETE	LOOSE PIECE			203816-3
	ON STRIP			203816-2
OB S OLETE	ON STRIP			203816-1
	REMARKS	FINISH	MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 3-29-05 CHK D.MILLER 3-29-05 APVD D.MILLER 3-29-05		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 [0.13] 4 PLC ± .0015 [0.038] ANGLES ± -		NAME PIN CONTACT ASSY,SIZE 20 (20-24 AWG) -	
MATERIAL SEE TABLE		FINISH SEE TABLE			
		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		SIZE A2	CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO C-203816	RESTRICTED TO -
				SCALE 10:1	SHEET 1 OF 1
				REV Y	