




FCIconnect.com

Copyright FCI

PRODUCT NO.
SEE TABLE



NOTES:

1. MADE IN ACCORDANCE WITH PRODUCT SPECIFICATION BUS-12-001 AND PURCHASE SPECIFICATION BUS-10-001.
2. COLOR GRAY WITH RED TRACER ON EDGE OF FIRST POSITION.
3. UL-LISTED STYLE 2651, CSA CERTIFIED. (LATEST REVISION)

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE			
title													
tolerances unless otherwise specified													
angles													
linear													
scale 1:1													
F	—	JWB	11/7/90			.XX±.01/.3		INCH/MM		#28 AWG STRANDED DOUBLE SCALLOPE			
G	V22247	MSC	6/5/92			.XXX±.005/.13				PVC ROUND CONDUCTOR CANBLE			
H	V82042	RGD	11/2/98	0'±2'		.XXX±.0020/.05		scale 1:1					
J	M06-0282	MHT	7/26/06	dr	J.W.BLAIR	11/7/90			dwg no		sheet 1 of 2 size		
				enr	M.SMYK	11/7/90			76825		A3		
				chr	M.SMYK	11/7/90							
				appd	M.SMYK	11/7/90			type		Product	Customer	
sheet index		revision sheet		J	J								
				1	2								

form: A3

PRODUCT NO.
76825-XXX

76825-XXX

NO. OF CONDUCTORS
(MIN. 6, MAX 64)
LENGTH

TOLERANCE FOR DIMS		
NO. OF CONDUCTORS	DIM. A±	DIM. B±
9 THRU 15	.007/.18	.010/.25
16 THRU 37	.009/.23	.015/.38
38 THRU 64	.011/.28	.015/.38

X	MIN. LENGTH FT/M
0	100/30.48
1	100/30.48
3	300/91.44
4	300/91.44

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE					
ltr	ecn	no	dr	date	tolerances unless otherwise specified					INCH/MM scale 1:1		title #28 AWG STRANDED DOUBLE SCALLOPE PVC ROUND CONDUCTOR CANBLE			
J					angles	linear	.XX±.01/.3								
								.xxx±.005/.13							
					0'±2'			xxxx±.0020/.05							
					dr	J.W.BLAIR	11/7/90								
					enr	M.SMYK	11/7/90								
					chr	M.SMYK	11/7/90			dwg no		sheet 2 of 2 size			
					appd	M.SMYK	11/7/90			76825		A3			
sheet index		revision sheet								type		Product Customer Drawing			

form: A3