




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
G	ECN 99999: UPDATED DRAWING AND NEW FORMAT	2/8/10	D.FRISIELLO



RECOMMENDED PANEL OPENING
(MAX PANEL THICKNESS: 0.06")



JACKSCREW SPECIFICATION

NOTES:

MATERIAL:
SHELL: STEEL
CONTACTS: COPPER ALLOY
HARDWARE: BRASS
INSULATOR: PBT FIBER REINFORCED (UL94V-0 RATED)


FINISH:
SHELL: TIN/NICKEL PLATED
CONTACTS: GOLD FLASH PLATED, 1-5μ INCHES
HARDWARE: NICKEL PLATED

ELECTRICAL:
CURRENT RATING: 3 AMP
INSULATION RESISTANCE: 1000 MΩ MIN @500 VDC
DIELECTRIC WITHSTANDING VOLTAGE: 1000 VAC (FOR ONE MINUTE)



MISCELLANEOUS:
OPERATING TEMPERATURE RANGE: -55°C TO +105°C.
ALL CONTACTS WIRED STRAIGHT THROUGH.
COMPONENT SHALL BE TESTED FOR CONTINUITY.

LABELING:
PANTONE 2945 BLUE. "L-COM" FONT MyriaMM ITALIC.
"GENDER CHANGER" FONT ARIAL BOLD, TEXT HEIGHTS; .085"
TEXT COLOR; WHITE.

PACKAGING:
COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN
ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		 NORTH ANDOVER, MA 01845													
		DRAWN BY R.CARRICK		09/28/2002															
		DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.01 .XXX = ±.005		CHECKED BY T.CLARK		09/28/2002		CATEGORY D-SUBMINIATURE											
		ANGULAR TOLERANCES: ALL = ± 1°		APPROVED BY D.PARHAM		09/28/02		PRODUCT DESCRIPTION GENDER CHANGER, DB37 SLIM F/F											
		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY				SIZE B		FSCM NO. 43321		DWG. NO. DGB37F		REV. G							
		COLOR VARIATIONS MAY OCCUR				SCALE: 2:1								CAD FILE: DGB37F.SLDDRW				SHEET 1 OF 1	