



FCIconnect.com


Copyright FCI

PRODUCT NO.

SEE TABLE

NOTES:

- ① HOUSING MAT'L: FILLED POLYESTER.
FLAME RETARDANT PER UL 94V-0.
COLOR: BLACK.
- ② TERMINAL MATERIAL AND PLATING: SEE TABULATION.
3. RECOMMENDED PIN SIZE: $.025 \pm .001 / .64 \pm .03$ SQUARE.
RECOMMENDED PIN LENGTH: $.210 \pm .020 / 5.33 \pm .51$.
4. MARK FCI PART NUMBER AND DATE CODE LEGIBLE
ON TUBE LABEL.
- ⑤ ADD "LF" SUFFIX AT THE END OF PART NUMBER
FOR LEAD FREE OPTION.
- ⑥ THESE PRODUCTS MEET EUROPEAN UNION DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS DESCRIBED
IN GS-22-008.
7. THIS PART WILL WITHSTAND EXPOSURE TO 260°C PEAK
TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER,
INFRA-RED OR VAPOR PHASE SOLDER PROCESS.
- ⑧ "THIS PRODUCT HAS 100% TIN PLATING IN THE
INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER
GROWTH IN ALL INTERCONNECT ENVIRONMENTS."



mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family CARD CONN		
ltr	ecn no	dr	date	tolerances unless otherwise specified		scale 4:1	title		
X				angles	linear		VERT. CARD CONNECTOR .100/2.54 CTR., DBL ROW		
				0°±2°					
				dr	M.CLOUSER	3/25/94	dwg no		
				enr	H. SUNDY	3/25/94	sheet 2 of 6 size		
				chr	H. SUNDY	3/25/94	65781 A3		
				appd	H. SUNDY	3/25/94	type Product Customer Drawing		
sheet index	revision sheet								

	EXP	OBS
1	1	1
2	1	1
3	1	1
4	1	1
5	1	1
6	1	1
7	1	1
8	1	1
9	1	1
10	1	1
11	1	1
12	1	1
13	1	1
14	1	1
15	1	1
16	1	1
17	1	1
18	1	1
19	1	1
20	1	1
21	1	1
22	1	1
23	1	1
24	1	1
25	1	1
26	1	1
27	1	1
28	1	1
29	1	1
30	1	1
31	1	1
32	1	1
33	1	1
34	1	1
35	1	1
36	1	1
37	1	1
38	1	1
39	1	1
40	1	1
41	1	1
42	1	1
43	1	1
44	1	1
45	1	1
46	1	1
47	1	1
48	1	1
49	1	1
50	1	1
51	1	1
52	1	1
53	1	1
54	1	1
55	1	1
56	1	1
57	1	1
58	1	1
59	1	1
60	1	1
61	1	1
62	1	1
63	1	1
64	1	1
65	1	1
66	1	1
67	1	1
68	1	1
69	1	1
70	1	1
71	1	1
72	1	1
73	1	1
74	1	1
75	1	1
76	1	1
77	1	1
78	1	1
79	1	1
80	1	1
81	1	1
82	1	1
83	1	1
84	1	1
85	1	1
86	1	1
87	1	1
88	1	1
89	1	1
90	1	1
91	1	1
92	1	1
93	1	1
94	1	1
95	1	1
96	1	1
97	1	1
98	1	1
99	1	1
100	1	1

NOTES 5,6,8

NOTES 5,6,8

FClconnect.com

Copyright FCI

D

1

FCI

FCIconnect.com

Copyright FCI

1

2

3

4

5

6

PRODUCT NUMBER	SIZE	DIM A	DIM B	MATERIAL AND PLATING	DIM C	LEAD FREE OPTION
65781-073				UNASSIGNED		
-074	2X2	.100 / 2.54	.200 / 5.08	BODY MAT'L: Cu Ni 10u"/.25u Au FLASH INSIDE BODY CONTACT AREA ONLY WITH .001/.03 MIN HIGH GOLD DOT. SPRING PLATING: GOLD FLASH SPRING MAT'L: BeCu HEAT TREAT	.140/3.56	NOTE 5,6
-075	2X3	.200 / 5.08	.300 / 7.62			
-076	2X4	.300 / 7.62	.400 / 10.16			
-077	2X5	.400 / 10.16	.500 / 12.70			
-078	2X6	.500 / 12.70	.600 / 15.24			
-079	2X7	.600 / 15.24	.700 / 17.78			
-080	2X8	.700 / 17.78	.800 / 20.32			
-081	2X9	.800 / 20.32	.900 / 22.86			
-082	2X10	.900 / 22.86	1.000 / 25.40			
-083	2X11	1.000 / 25.40	1.100 / 27.94			
-084	2X12	1.100 / 27.94	1.200 / 30.48			
-085	2X13	1.200 / 30.48	1.300 / 33.02			
-086	2X14	1.300 / 33.02	1.400 / 35.56			
-087	2X15	1.400 / 35.56	1.500 / 38.10			
-088	2X16	1.500 / 38.10	1.600 / 40.64			
-089	2X17	1.600 / 40.64	1.700 / 43.18			
-090	2X18	1.700 / 43.18	1.800 / 45.72			
-091	2X19	1.800 / 45.72	1.900 / 48.26			
-092	2X20	1.900 / 48.26	2.000 / 50.80			
-093	2X21	2.000 / 50.80	2.100 / 53.34			
-094	2X22	2.100 / 53.34	2.200 / 55.88			
-095	2X23	2.200 / 55.88	2.300 / 58.42			
-096	2X24	2.300 / 58.42	2.400 / 60.96			
-097	2X25	2.400 / 60.96	2.500 / 63.50			
-098	2X26	2.500 / 63.50	2.600 / 66.04			
-099	2X27	2.600 / 66.04	2.700 / 68.58			
-100	2X28	2.700 / 68.58	2.800 / 71.12			
-101	2X29	2.800 / 71.12	2.900 / 73.66			
-102	2X30	2.900 / 73.66	3.000 / 76.20			
-103	2X31	3.000 / 76.20	3.100 / 78.74			
-104	2X32	3.100 / 78.74	3.200 / 81.28	BODY MAT'L: Cu Ni 10u"/.25u Au FLASH INSIDE BODY CONTACT AREA ONLY WITH .001/.03 MIN HIGH GOLD DOT. SPRING PLATING: GOLD FLASH SPRING MAT'L: BeCu HEAT TREAT		
-105	2X33	3.200 / 81.28	3.300 / 83.82			
-106	2X34	3.300 / 83.82	3.400 / 86.36			
-107	2X35	3.400 / 86.36	3.500 / 88.90			
65781-108	2X36	3.500 / 88.90	3.600 / 91.44		.140/3.56	NOTE 5,6

mat'l. code

surfaceISO 1302 ✓toleranceISO 406ISO 1101

projection

product familyCARD CONN

title

VERT. CARD CONNECTOR
.100/2.54 CTR., DBL ROW

dwg no

sheet5 of 6

size

A3

type

Product Customer Drawing

revision

sheet

dr

M.CLOUSER

3/25/94

enr

H. SUNDY

3/25/94

chr

H. SUNDY

3/25/94

app

H. SUNDY

3/25/94

sheet index

revision

sheet

1

2

3

4

5

6

form: A3

PDS: Rev :X

STATUS:Released

Printed: Apr 09, 2013

PRODUCT NUMBER	SIZE	DIM A	DIM B	MATERIAL AND PLATING	DIM C	LEAD FREE OPTION
65781-149	2X5	.400/10.16	.500/12.70	BRASS 100u"/2.54u THICK SN PLATE SPRING MAT'L: BeCu HEAT TREATED SPRING PLATING: 30u"/76u MIN ELECTROLESS TIN	.115/2.92	NOTES 5,6,8
65781-151	2X7	.600/15.24	.700/17.78		.115/2.92	
65781-152	2X8	.700/17.78	.800/20.32		.115/2.92	
65781-153	2X13	1.200 / 30.48	1.300 / 33.02	CONTACT BODY MATERIAL: BRASS CONTACT BODY PLATING: 30u"/0.76u MIN GOLD INSIDE CONTACT AREA AND GOLD FLASH ON TAILS OVER 50u"/1.27u MIN NICKEL SPRING MATERIAL: BeCu HEAT TREATED SPRING PLATING: GOLD FLASH ON CONTACT AREA	.140/3.56	NOTE 5,6
65781-154	2X15	1.400 / 35.56	1.500 / 38.10		.140/3.56	
65781-155	2X17	1.600 / 40.64	1.700 / 43.18		.140/3.56	
65781-156	2X18	1.700 / 43.18	1.800 / 45.72		.140/3.56	
65781-157	2X20	1.900 / 48.26	2.000 / 50.80		.140/3.56	
65781-158	2X30	2.900 / 73.66	3.000 / 76.20		.140/3.56	
65781-159	2X10	.900 / 22.86	1.000 / 25.40		.140/3.56	
65781-160	2X5	.400 / 10.16	.500 / 12.70		.140/3.56	