








REVISIONS					
LOC	DIST	P	LTR	DESCRIPTION	DATE
-	-	B		REVISED PER ECR-16-003314	18JUL2016

DWN	APVD
BW	GJ



RECOMMENDED PANEL OPENING DEMENSIONS
FOR CAP HOUSING 2*6 AND 2*5 AND 2*4 POSITIONS
(TOLERANCE: ±0.15mm)

RECOMMENDED PANEL OPENING DEMENSIONS
FOR CAP HOUSING 2*3 POSITION
(TOLERANCE: ±0.15mm)



1. MATERIAL:
LEVEL A: PA6 GLASS FILLED, COMPLY WITH GLOW WIRE REQUIREMENTS FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30 (GWT),UL 94V-0
LEVEL B: PBT GLASS FILLED, HOT WIRE IGNITION (HWI) VERSION ARE MOLDED IN A RESIN THAT COMPLIES WITH TE HOT WIRE IGNITION TEST 109-32026 AND ARE RECOMMENDED FOR USE WITH HWI HOUSINGS THAT ALSO COMPLY, UL 94V-0

2. MATERIAL MARK:
LEVEL A:GWT,LEVEL B:HWT

3. APPLICABLE CONTACT P/N
TAB CONTACT:1971238/1971780/82/84/86/88-*,2238067-*

4. MATING CONN, P/N
PLUG HSG: *-2232266-*
TPA (LOCK PLATE): *-1971778-*







5. RECOMMENDED PANEL THICKNESS:1.0~2.0mm

6. THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING.

POS	A	B	C	D	E
2*6	39.70	45.5	37.30	42.70	37.80
2*5	33.70	39.5	31.30	36.70	31.80
2*4	27.70	33.5	25.30	30.70	25.80
2*3	21.70	27.5	19.30		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TOMMY WU 26MAR2013	 TE Connectivity	
		CHK HAPYE WU 26MAR2013		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.35 1 PLC ±0.25 2 PLC ±0.25 3 PLC ±0.25 4 PLC ±0.25 ANGLES ±0.25 FINISH	APVD YUZHONG MAO 26MAR2013	NAME CAP HOUSING,PANEL MOUNT,DOUBLE ROW POWER TRIPLE LOCK	
		PRODUCT SPEC 108-106118		
MATERIAL		APPLICATION SPEC 114-106118	SIZE CAGE CODE DRAWING NO A100779C=2232264	
		WEIGHT		
Customer Drawing		SCALE	SHEET 1 OF 2	REV B





LOC		DIST		REVISONS			
P	LYR	DESCRIPTION			DATE	OWN	APVD
-	-	SEE SHEET 1			-	-	-







2*5 POSITIONS

2*4 POSITIONS





2*3 POSITIONS





KEYING FOR 2*5 POS.







KEYING FOR 2*4 POS.



KEYING FOR 2*3 POS.



2*6 POSITIONS



KEYING FOR 2*6 POS.

2*6	LEVEL A	DARK GREY	KEY A	5-2232264-6
		BROWN	KEY B	6-2232264-6
		GREEN	KEY C	7-2232264-6
		ORANGE	KEY D	8-2232264-6
2*5	LEVEL A	DARK GREY	KEY A	5-2232264-5
		BROWN	KEY B	6-2232264-5
		GREEN	KEY C	7-2232264-5
		ORANGE	KEY D	8-2232264-5
2*4	LEVEL A	DARK GREY	KEY A	5-2232264-4
		BROWN	KEY B	6-2232264-4
		GREEN	KEY C	7-2232264-4
		ORANGE	KEY D	8-2232264-4
2*3	LEVEL A	DARK GREY	KEY A	5-2232264-3
		BROWN	KEY B	6-2232264-3
		GREEN	KEY C	7-2232264-3
		ORANGE	KEY D	8-2232264-3
	LEVEL B	BLACK	KEY A	1-2232264-1
POS.	MATERIAL	COLOR	KEY	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TOMMY.WU 26MAR2013		 TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK HAPYE.WU 26MAR2013			
DIMENSIONS: mm		APVD YUHHONG.MAO 26MAR2013		NAME CAP HOUSING,PANEL MOUNT,DOUBLE ROW POWER TRIPLE LOCK	
		PRODUCT SPEC 108-106118			
MATERIAL		APPLICATION SPEC 114-106118		SIZE CAGE CODE DRAWING NO A100779C=2232264	
		FINISH			
		Customer Drawing		SCALE	
				SHEET 2 OF 2	
				REV B	