


ENERGIZER NO. X95




Industry Standard Dimensions in mm (inches)




Chemical System:	Alkaline Zinc-Manganese Dioxide (Zn/MnO ₂) (No Added Mercury or Cadmium)
Designation:	ANSI-13A, IEC-LR20
Battery Voltage:	1.5 Volts
Internal Resistance:	173 Milliohms (Fresh)
Operating Temp:	-18°C to 55°C (0°F to 130°F)
Average Capacity:	21,500 mAh (to 0.8 volts) (Rated capacity at 25 mA continuous drain)
Average Weight:	148.0 grams (5.2 oz.)
Volume:	55.9 cubic centimeters (3.4 cubic inch)
Cell:	One No. X3-350 (size 'D')
Jacket:	Plastic Label
Shelf Life:	7 years (80% of rated capacity)


TEMPERATURE EFFECTS Typical Service to 0.8 Volts



CONSTANT RESISTANCE PERFORMANCE Typical Service



CONSTANT CURRENT DISCHARGE Typical Service







Important Notice

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Copyright © Eveready Battery Co. - All rights reserved

ENERGIZER NO. X95**Industry Standard Tests @ 20° C****PORTABLE LIGHTING**
1.5 ohm - HIF**TOY**
2.2 ohm - 1hr/day**PORTABLE STEREO**
600 mA - 2 hr/day**PORTABLE LIGHTING**
2.2 ohm - LIF**RADIO**
10 ohm - 4 hr/day**Important Notice**

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Copyright © Eveready Battery Co. - All rights reserved