

3-Terminal 500mA Negative Voltage Regulator




1. Ground
2. Input (tab)
3. Output

The TS79M00 series of fixed output negative voltage regulators are intended as complements to the popular TS78M00 series device. These negative regulators are available in the same seven-voltage options as the TS7900 devices. In addition, one extra voltage option commonly employed in MECL systems is also available in the negative TS79M00 Series. Available in fixed output voltage options from -5.0 to -24 volts, these regulators employ current limiting, thermal shutdown, and safe-area compensation--making them remarkably rugged under most operating conditions. With adequate heat sinking they can deliver output currents in excess of 0.5 ampere.

- Output Voltage: -5 & -12V
- Output current up to 0.5A
- No external components required
- Internal thermal overload protection
- Internal short-circuit current limiting
- Output transistor safe-area compensation
- Output voltage offered in 4% tolerance

Part Number	Package	Quantity
TS79M__CZ C0	TO-220	50pcs / Tube
TS79M__CP RO	TO-252	2.5Kpcs / 13" Reel

Note: Where __ denote voltage option



A common ground is required between the input and the output voltages. The input voltage must remain typically 2.0V above the output voltage even during the low point on the Input ripple voltage.

XX = these two digits of the type number indicate voltage.

* = Cin is required if regulator is located an appreciable distance from power supply filter.

** = Co is not needed for stability; however, it does improve transient response.

(Ta = 25°C unless otherwise noted)

Parameter	Symbol	Value	Unit
Input Voltage	V_{IN}	-35	V
Power Dissipation	P_D	Internal Limited	W
Operating Junction Temperature	T_J	0~+125	°C
Storage Temperature Range	T_{STG}	-65~+150	°C

Note: Follow the derating curve

3-Terminal 500mA Negative Voltage Regulator

($V_{in} = -10V$, $I_{out} = 350mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{in} = 0.33\mu F$, $C_{out} = 0.1\mu F$; unless otherwise specified.)







Output voltage	Vout	Tj=25°C		-4.80	-5	-5.20	V
		-7.5V≤Vin≤-20V, 5mA≤Iout≤500mA, PD≤5W		-4.75	-5	-5.25	
Line Regulation	REGline	Tj=25°C	-7.5V≤Vin≤-25V	--	7	50	mV
			-8V≤Vin≤-18V	--	2	30	
Load Regulation	REGload	Tj=25°C	5mA≤Iout≤500mA	--	20	100	
			250mA≤Iout≤200mA	--	10	50	
Quiescent Current	Iq	Iout=0, Tj=25°C		--	4	8	mA
Quiescent Current Change	ΔIq	-7.5V≤Vin≤-25V		--	--	1	
		5mA≤Iout≤500mA		--	--	0.5	
Output Noise Voltage	Vn	10Hz≤f≤100KHz, Tj=25°C		--	40	--	μV
Ripple Rejection Ratio	RR	f=120Hz, -8V≤Vin≤-18V		54	66	--	dB
Voltage Drop	Vdrop	Iout=500mA, Tj=25°C		--	2	--	V
Peak Output Current	Io peak	Tj=25°C		--	2.1	--	A
Temperature Coefficient of Output Voltage	ΔVout/ ΔTj	Iout=5mA, 0°C≤Tj≤125°C		--	-0.1	--	mV/°C

($V_{in} = -19V$, $I_{out} = 350mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{in} = 0.33\mu F$, $C_{out} = 0.1\mu F$; unless otherwise specified.)


Output voltage	Vout	Tj=25°C		-11.53	-12	-12.48	V
		-14.5V≤Vin≤-27V, 5mA≤Iout≤500mA, PD ≤5W		-11.42	-12	-12.60	
Line Regulation	REGline	Tj=25°C	-14.5V≤Vin≤-30V	--	10	240	mV
			-15V≤Vin≤-19V	--	3	120	
Load Regulation	REGload	Tj=25°C	5mA≤Iout≤500mA	--	12	240	
			250mA≤Iout≤200mA	--	4	120	
Quiescent Current	Iq	Tj=25°C, Iout=0		--	4.3	8	mA
Quiescent Current Change	ΔIq	-14.5V≤Vin≤-30V		--	--	1	
		5mA≤Iout≤500mA		--	--	0.5	
Output Noise Voltage	Vn	10Hz≤f≤100KHz, Tj=25°C		--	75	--	μV
Ripple Rejection Ratio	RR	f=120Hz, -15V≤Vin≤-25V		55	70	--	dB
Voltage Drop	Vdrop	Iout=500mA, Tj=25°C		--	2	--	V
Peak Output Current	Io peak	Tj=25°C		--	2.1	--	A
Temperature Coefficient of Output Voltage	ΔVout/ ΔTj	Iout=5mA, 0°C≤Tj≤125°C		--	-1	--	mV/°C

- Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible, and thermal effects must be taken into account separately.
- This specification applies only for DC power dissipation permitted by absolute maximum ratings.


3-Terminal 500mA Negative Voltage Regulator




3-Terminal 500mA Negative Voltage Regulator



3-Terminal 500mA Negative Voltage Regulator




TO-220 DIMENSION				
DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	10.000	10.500	0.394	0.413
B	3.740	3.910	0.147	0.154
C	2.440	2.940	0.096	0.116
D	-	6.350	-	0.250
E	0.381	1.106	0.015	0.040
F	2.345	2.715	0.092	0.058
G	4.690	5.430	0.092	0.107
H	12.700	14.732	0.500	0.581
I	8.382	9.017	0.330	0.355
J	14.224	16.510	0.560	0.650
K	3.556	4.826	0.140	0.190
L	0.508	1.397	0.020	0.055
M	27.700	29.620	1.060	1.230
N	2.032	2.921	0.080	0.115
O	0.255	0.610	0.010	0.024
P	5.842	6.858	0.230	0.270




- = Output Voltage
(=-5V, =-12V)
- = Year Code
- = Month Code
(=Jan, =Feb, =Mar, =Apr, =May, =Jun, =Jul, =Aug, =Sep,
=Oct, =Nov, =Dec)
- = Lot Code
- = Package Code for TO-220

3-Terminal 500mA Negative Voltage Regulator



DIM	TO-252 DIMENSION			
	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	2.3BSC		0.09BSC	
A1	4.6BSC		0.18BSC	
B	6.80	7.20	0.268	0.283
C	5.40	5.60	0.213	0.220
D	6.40	6.65	0.252	0.262
E	2.20	2.40	0.087	0.094
F	0.00	0.20	0.000	0.008
G	5.20	5.40	0.205	0.213
G1	0.75	0.85	0.030	0.033
G2	0.55	0.65	0.022	0.026
H	0.35	0.65	0.014	0.026
I	0.90	1.50	0.035	0.059
J	2.20	2.80	0.087	0.110
K	0.50	1.10	0.020	0.043
L	0.90	1.50	0.035	0.059
M	1.30	1.70	0.051	0.67



- = Output Voltage
(=-5V, =-12V)
- = Year Code
- = Month Code
(=Jan, =Feb, =Mar, =Apr, =May, =Jun, =Jul, =Aug, =Sep, =Oct, =Nov, =Dec)
- = Lot Code
- = Package Code for TO-252

3-Terminal 500mA Negative Voltage Regulator

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.