

	13	12	11	10	9	8	7	6	5	4	3	2	1			
J	ENG. NO.	PIN NO.	DIM. L	DIM. X	DIM. Z	DIM. G TYP BOTH ENDS									J	
I	A-2220-NA197	43294-0832	(35.05) 1.380	(16.00) .630	(16.13) .635	N/A									I	
	A-2220-NA502	43294-0833	(35.05) 1.380	(16.00) .630	(16.13) .635	(6.85) .270										
	A-2220-NAB502	43294-1100	(42.42) 1.670	(16.89) .665	(22.61) .890	(7.62) .300										
	A-2220-NB197	43294-1147	(44.45) 1.750	(18.24) .718	(23.29) .917	N/A										
H														H		
G	A-2220-NA197		A-2220-NA502		A-2220-NAB502		A-2220-NB197								G	
	PART NO.	ENG. NO.	PART NO.	ENG. NO.	PART NO.	ENG. NO.	PART NO.	ENG. NO.								
	09-57-1025	A-2220-2A197	09-78-1021	A-2220-2A502			A-2220-2AB502	09-57-1026	A-2220-2B197							
	09-57-1035	A-2220-3A197	09-78-1031	A-2220-3A502			A-2220-3AB502	09-57-1036	A-2220-3B197							
F	09-57-1045	A-2220-4A197	09-78-1041	A-2220-4A502			A-2220-4AB502	09-57-1046	A-2220-4B197							F
	09-57-1055	A-2220-5A197	09-78-1051	A-2220-5A502			A-2220-5AB502	09-57-1056	A-2220-5B197							
	09-57-1065	A-2220-6A197	09-78-1061	A-2220-6A502	09-78-1067		A-2220-6AB502	09-57-1066	A-2220-6B197							
	09-57-1075	A-2220-7A197	09-78-1071	A-2220-7A502			A-2220-7AB502	09-57-1076	A-2220-7B197							
E	09-57-1085	A-2220-8A197	09-78-1081	A-2220-8A502	09-78-1087		A-2220-8AB502	09-57-1086	A-2220-8B197							E
	09-57-1095	A-2220-9A197	09-78-1091	A-2220-9A502			A-2220-9AB502	09-57-1096	A-2220-9B197							
	09-57-1105	A-2220-10A197	09-78-1101	A-2220-10A502	09-78-1107		A-2220-10AB502	09-57-1106	A-2220-10B197							
	09-57-1115	A-2220-11A197	09-78-1111	A-2220-11A502			A-2220-11AB502	09-57-1116	A-2220-11B197							
D	09-57-1125	A-2220-12A197	09-78-1121	A-2220-12A502	09-78-1127		A-2220-12AB502	09-57-1126	A-2220-12B197							D
	09-57-1135	A-2220-13A197	09-78-1131	A-2220-13A502			A-2220-13AB502	09-57-1136	A-2220-13B197							
	09-57-1145	A-2220-14A197	09-78-1141	A-2220-14A502			A-2220-14AB502	09-57-1146	A-2220-14B197							
	09-57-1155	A-2220-15A197	09-78-1151	A-2220-15A502	09-78-1157		A-2220-15AB502	09-57-1156	A-2220-15B197							
C	09-57-1165	A-2220-16A197	09-78-1161	A-2220-16A502			A-2220-16AB502	09-57-1166	A-2220-16B197							C
	09-57-1175	A-2220-17A197	09-78-1171	A-2220-17A502			A-2220-17AB502	09-57-1176	A-2220-17B197							
	09-57-1185	A-2220-18A197	09-78-1181	A-2220-18A502			A-2220-18AB502	09-57-1186	A-2220-18B197							
B														B		
A														A		
															</	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

09-57-1115