









DATE	DESCRIPTION	REV.
2.25.10	CHANGE AS PER ECN 10-017	A
6.01.11	CHANGE AS PER ECN 11-077	B
11.05.12	CHANGE AS PER ECN 12-155	C
2.20.13	CHANGE AS PER ECN 13-019	D





Top Shell




Insulator Body



Bottom Shell



Supplied Unassembled



Notes:

Material:

Shell: Steel, Nickel Plate.

Insulator: PBT, UL 94-V0 (Color Black)

Contacts: Phosphor Bronze

Finish:

Contact Area: Gold Plate over Nickel Plate
on Solder Tail: Tin Plate over Nickel Plate

Electrical Specifications

Rated Voltage: 30V AC (rms)


Contact Current Rating: 1.5 Amp

Contact Resistance: 30 milliohms Max.

Dielectric Withstanding: 100V AC

Operating Temperature: -30°C to 85°C

ACTUAL SIZE



THIS DOCUMENT IS THE PROPERTY OF
KEYSTONE ELECTRONICS CORP. AND
SHALL NOT BE REPRODUCED, DISTRIBUTED
OR USED AS A BASIS FOR MANUFACTURE
WITHOUT PRIOR WRITTEN PERMISSION
FROM KEYSTONE ELECTRONICS CORP.

KEYSTONE ELECTRONICS CORP.				
www.keyelco.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900				
PART NAME		MICRO USB PLUG		
MATERIAL		AS NOTED		
FINISH		AS NOTED		
AS NOTED		DRN BY	NT	DATE
		APPD	LN	SCALE
TOLERANCES		INCH	[MM]	CODE
DECIMAL		± .010	[± 0.25]	C
ANGULAR		± 1°		
UNLESS OTHERWISE SPECIFIED		DWG NO.		
		941		