






NOTES:

- 1 MATERIAL: LCP, COLOR: NATURAL
CONTACT: BERYLLIUM COPPER
SOLDER BALL: SEE TABLE
FILM TAPE: KAPTON WITH SILICONE ADHESIVE
- 2 FINISH: CONTACT: GOLD (SEE TABLE) ON MATING AREA OVER
NICKLE ON ENTIRE CONTACT.
3. PRODUCT IS PACKAGE ON TAPE AND REEL.
- 4 PRELIMINARY PART.
- 5 DIAGRAM REPRESENTS THE REELING DIRECTION OF THE PACKAGED CONNECTORS. THERE ARE 10 EMPTY POCKETS AT THE BEGINNING OF THE REEL AND 15 EMPTY POCKETS AT THE END OF THE REEL.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
C		REV PER ECO 18-010457	7-24-18	CT	CJ
D		REVISED PER ECO-19-004671	26MAR2019	DCB	RL
E		REV PER ECN-25-348658	15OCT2025	LP	DLG



4	2102429-4	15	0.76µm	11	LEAD FREE PER SAC405	1-2102430-6
4	2102429-3	15	0.76µm	11	TIN LEAD	1-2102430-5
4	2102429-2	15	1.27µm	11	LEAD FREE PER SAC405	1-2102430-4
4	2102429-1	15	1.27µm	11	TIN LEAD	1-2102430-3
	2102429-4	18	0.76µm	14	LEAD FREE PER SAC405	1-2102430-2
	2102429-3	18	0.76µm	14	TIN LEAD	1-2102430-1
	2102429-2	18	1.27µm	14	LEAD FREE PER SAC405	1-2102430-0
	2102429-1	18	1.27µm	14	TIN LEAD	2102430-9
4	2102429-4	12	0.76µm	8	LEAD FREE PER SAC405	2102430-8
4	2102429-3	12	0.76µm	8	TIN LEAD	2102430-7
	2102429-4	10	0.76µm	6	LEAD FREE PER SAC405	2102430-6
	2102429-3	10	0.76µm	6	TIN LEAD	2102430-5
4	2102429-2	12	1.27µm	8	LEAD FREE PER SAC405	2102430-4
4	2102429-1	12	1.27µm	8	TIN LEAD	2102430-3
	2102429-2	10	1.27µm	6	LEAD FREE PER SAC405	2102430-2
	2102429-1	10	1.27µm	6	TIN LEAD	2102430-1
	MATING PART NUMBER	STACK HEIGHT (mm)	GOLD PLATING THICKNESS	H MAX REF	SOLDER BALL MATERIAL	PART NUMBER

